

BRXL-16U3

Specifications

BD-R XL	TL/QL 6x Read/Write
BD-R	SL 12x Read/16x Write, DL 8x Read/12x Write
BD-R (LTH)	SL 6x Read/Write
BD-RE XL	TL 4x Read/2x Write
BD-RE	SL 8x Read/2x Write, DL 6x Read/2x Write
BD-ROM	SL 12x Read, DL 8x Read
DVD-R	SL 16x Read/Write, DL 12x Read/8x Write
DVD+R	SL 16x Read/Write, DL 12x Read/8x Write
DVD-RW	12x Read/6x Write
DVD+RW	12x Read/8x Write
DVD-RAM	5x Read/Write
DVD-ROM	SL 16x Read, DL 12x Read
DVD-VIDEO	SL 12x Read, DL 8x Read
CD-R	48x Read/Write
CD-RW	40x Read/24x Write
CD-ROM	48x Read
Power Supply	US : AC 100-120 V 50/60 Hz (external) Other region : AC 100-240 V 50/60 Hz (external)
Dimensions	220 x 160 x 50 mm
Weight	max 1200 g
Operating Environment	5° - 35° C 20 - 80% humidity (no condensation)
Power Consumption	~36 Watts
Windows Compatibility	Windows 10 (32-bit and 64-bit) Windows 8.1 (32-bit and 64-bit) Windows 8 (32-bit and 64-bit) Windows 7 (32-bit and 64-bit) Windows Vista (32-bit and 64-bit) Windows XP (32-bit)

Regulatory Compliance Information

For Customers in the United States

FCC Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to Part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

Reorient or relocate the receiving antenna.

Increase the separation between the equipment and receiver.

Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.

Consult the dealer or an experienced radio/TV technician for help.

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Only use the cables and accessories that are included in the package. Don't use other accessories or cables unless specifically instructed to in the documentation.

Proposition 65

WARNING:

This product and its components contain chemicals known to the State of California to cause cancer and birth defects, or reproductive harm. Wash hands after handling.

For Customers in Europe

AC Adapter

Asian Power Devices Inc. WA-36A12 or WA-36A12R

For Customers in Canada

CAN ICES-3 (B)/NMB-3(B)

For Customers in Korea

KC

기종별	사 용 자 안 내 문
B급 기기(가정용 정보통신기기)	이 기기는 가정용(B급) 전자파적합기기로서 주로 가정에서 사용하는 것을 목적으로 하며, 모든지역에서 사용할 수 있습니다.