

## ESG

### ESG 15/10 MC NE WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from the following manufacturers:

- Siemens
- Télémecanique
- ABB
- Beckhoff
- Lumberg
- Tags for all-purpose usage; self-adhesive or clip-on tags, depending on the type

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

Please note that these markers are not intended for printing with the SpeedMarking laser.

#### General ordering data

Type	ESG 15/10 MC NE WS
Order No.	<a href="#">2047360000</a>
Version	ESG, Device markers, 10 x 15 mm, Polyamide 66, Colour: White
GTIN (EAN)	4050118411171
Qty.	160 pc(s).
compatible printer	<a href="#">1324380000</a> <a href="#">1139400000</a> <a href="#">1925000000</a>

**Data sheet**

**ESG  
ESG 15/10 MC NE WS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Length	10 mm	Length (inches)	0.394 inch
Width	15 mm	Width (inches)	0.591 inch
Net weight	0.46 g		

**General data**

Application/manufacturer	Siemens ET 200SP	Colour	White
Length	10 mm	Material	Polyamide 66
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
UL 94 flammability rating	V-2	Width	15 mm

**Classifications**

ETIM 6.0	EC001288	eClass 6.2	27-14-91-29
eClass 9.0	27-40-06-29		

**Approvals**

ROHS	Conform
------	---------

**ESG**  
**ESG 15/10 MC NE WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 1429-0  
Fax: +49 5231 14292083  
[www.weidmueller.com](http://www.weidmueller.com)

