### MediaStation DVD writer





DVSM-PT58U2VB

# MediaStation DVD Writer

Buffalo Technology's MediaStation DVD writer (DVSM-PT58U2VB series) is a slim portable solution for reading and writing CDs and DVDs. Buffalo's DVD writer even writes M-DISC™ DVDs – currently the most archival and long-lasting disc media available, expected to last 1,000 years!

The DVSM-PT58U2VB is perfect for laptop and netbook users who travel frequently or home or office users looking for a small, unobtrusive, and elegant solution. The lightweight, compact, and slim design means it easily and comfortably fits into any travel bag.

Buffalo Technology's MediaStation DVD writer is USB powered, and with integrated USB cables, an AC adapter is not required.

The DVD drive also comes complete with Cyberlink Software which enables writing content to CD-Rs and DVDs, making it the perfect solution for anyone on the move.



#### Features and Benefits

- Watch DVDs or burn data to CDs or DVDs for backup anytime, anywhere — at home or on-the-go
- USB Bus Powered No additional power supply required
- Integrated USB Cables snap to the chassis for easy mobility
- LED power and status indicator
- Includes CyberLink Software for writing data content to CD-Rs and DVDs
- 2-year warranty



### MediaStation DVD writer



#### **Portable DVD Writer**

DVSM-PT58U2VB

## Specifications

Interface	
Standard Compliance	USB 2.0
'	USB Mini-B
Connector Type	
Performance	Max 480 Mbps
DVD Read / Write Speeds	
DVD-R SL	8x/8x
DVD-R DL	6x/6x
DVD+R SL	8x/8x
DVD+R DL	6x/6x
DVD-RW	8x/6x
DVD+RW	8x/8x
DVD-RAM	5x/5x
DVD-ROM SL/DL	8x Read
CD Read / Write Speeds	
CD-R	24x/24x
CD-RW	24x/16x
CD-ROM	24x Read
Audio CD/Video CD	10x Read
Other	
Enabled Devices	USB3.0/2.0 Windows PC, Mac (Intel processor model), Surface Pro 3 (with power supply)
Supported OS	Windows 8.1*/8*/7*/Vista*, Windows RT8.1/RT, MacOS X 10.7 and later
Included Software	Cyberlink Media Suite (Power2Go 8, PhotoDirector 4 LE,
	PowerMediaPlayer, MediaShow 6 Trial), Adobe Reader
Dimensions (WxDxH)	138 x 14.4 x 152 mm
Weight	220 grams
Operating Environment	5-35°C, 20-80% (non-condensing)
Power Consumption	~ 7.5 W
Power Supply	USB Bus Powered

Product Codes
DVSM-PT58U2VB-EU

#### About Buffalo

Buffalo Technology is a leading global provider of award-winning storage, networking and multimedia solutions for the home and small business environments as well as for system builders and integrators. With more than three decades of networking and computer peripheral experience, Buffalo has proven its commitment to delivering innovative solutions that have put the company at the forefront of infrastructure technology.

© Buffalo Inc. 2015. BUFFALO logo, AirStation, Nfiniti, AOSS, TeraStation, LinkStation, DriveStation and MiniStation are either trademarks or registered trademarks of Melco Holdings Inc. or Buffalo Inc. Microsoft Windows and Microsoft logo are either registered trademarks or trademarks of Microsoft Corporation in United States and/or other countries. The names and logos of other companies mentioned herein belong to their respective owners. The information within this datasheet is subject to change without notice. All rights reserved. E & OE.

<sup>\*32</sup>bit/64bit support