

16x External Blu-ray™ Drive

Portable Blu-Ray™ Writer

BUFFALO™

BRXL-PT6U2VB

Big Blu-ray™ Features from a Small Sleek Device

Buffalo Technology's MediaStation Portable Blu-ray Writer (BRXL-PT6U2VB) is a slim portable solution for storing, editing, and watching high-definition content. Blue-ray also allows users to burn and store huge data files – up to 128 GB capacity on a single BDXL format disc.

The BRXL-PT6U2VB is perfect for laptop and netbook users who travel frequently or home or office users looking for a small, unobtrusive, and elegant solution. The lightweight, compact, and slim design with integrated USB cables means it easily and comfortably fits into any travel bag without the hassle of additional loose cords and plugs. With Buffalo's BRXL-PT6U2VB everything you need is ready-to-go whenever and wherever you do.

Buffalo's Blu-ray writer also comes with a rich software suite from CyberLink® including video editing, authoring, 3D BD player and video playback functionality. The BRXL-PT6U2VB can even write M-DISC format – currently the most archival and long-lasting disc media available, expected to last 1,000 years!



Features and Benefits

- 16x External Blu-ray™ Drive
- Problem-free and fast read/write speeds for huge amounts of data
- Exceedingly Fast with Exceptional Playback and Burning Ability
- Ideal for users seeking the best Blu-ray playback and burning performance
- Great for periodic data backups and archive creation
- Quick and simple support for BDXL format discs:
 - Extra-large capacities up to 128 GB
 - For home use this equals about 17,060 photos or 1,000 minutes of HD video (AVCHD)
- Backward compatible with DVD & CD formats:
 - only one device needed for all optical media
- Includes CyberLink Software suite for editing, authoring, and additional functionalities
- 2 year Warranty, certified in Japan



16x External Blu-ray™ Drive



Portable Blu-Ray™ Writer

BRXL-PT6U2VB

Specifications

Interface	
Standard Compliance	USB 2.0
Connector Type	USB Mini-B
Performance	Max 480 Mbps
Read / Write Speeds	
Blu-Ray Disc	
BD-R SL/DL	6x/6x
BD-R TL/QL	4x/4x
BD-RE SL/DL	6x/2x
BD-RE TL	4x/2x
BD-ROM SL/DL	6x Read
DVD	
DVD-R SL	8x/8x
DVD-R DL	8x/6x
DVD+R SL	8x/8x
DVD+R DL	8x/6x
DVD-RW	8x/6x
DVD+RW	8x/8x
DVD-RAM	5x/5x
DVD-ROM SL/DL	8x Read
DVD-VIDEO SL/DL	4x Read
CD	
CD-R	24x/24x
CD-RW	24x/16x
CD-ROM	24x Read
Audio CD/Video CD	10x Read
Other	
Enabled devices	USB3.0/2.0 Windows PC, Mac (Intel processor model), Surface Pro 3 (with power supply)
Supported OS	Windows 8.1/8/7/Vista, Windows RT8.1/RT, MacOS X 10.7 and later
Included Software	Cyberlink Media Suite (Power2Go 8, PhotoDirector 4 LE, PowerMediaPlayer, MediaShow 6 Trial), Adobe Reader
Dimensions (WxDxH)	138 x 14.4 x 152 mm (W x H x D)
Weight	220 grams
Operating environment	5–35°C, 20–80% (non-condensing)
Power consumption	~ 7.5 W
Power supply	USB Bus Powered

Product Codes

BRXL-PT6U2VB-EU

*32bit/64bit support

About Buffalo

Buffalo Technology is a leading global provider of award-winning storage, networking and multimedia solutions for the home and small business environments as well as for system builders and integrators. With more than three decades of networking and computer peripheral experience, Buffalo has proven its commitment to delivering innovative solutions that have put the company at the forefront of infrastructure technology.

© Buffalo Inc. 2015. BUFFALO logo, AirStation, Nfiniti, AOSS, TeraStation, LinkStation, DriveStation and MiniStation are either trademarks or registered trademarks of Melco Holdings Inc. or Buffalo Inc. Microsoft Windows and Microsoft logo are either registered trademarks or trademarks of Microsoft Corporation in United States and/or other countries. The names and logos of other companies mentioned herein belong to their respective owners. The information within this datasheet is subject to change without notice. All rights reserved. E & OE.