



SuperSpeed USB 3.1 Gen 1 C Hub

4 A Ports, Bus Power

Part No.: **162746**

Quickly connect more USB Type-A peripherals to type-C devices

The Manhattan SuperSpeed USB 3.1 Type-C Hub easily adds four SuperSpeed Type-A ports to any USB type-C compatible device, expanding connectivity for keyboards, mice, external memory and other peripherals. Its SuperSpeed ports are backward compatible to support older devices, provide data transfer speeds up to 5 Gbps for external storage, printing and other activities, and capable of charging and powering at 5V/1A output.

Easy to add connectivity

A durable case, compact size and bus-power make it easily transportable to add USB connectivity almost anywhere. Installation is simple with Plug and Play and hot-swappable capabilities, and a built-in USB cable quickly connects the Manhattan SuperSpeed USB 3.1 Type-C Hub to any USB type-C port.

Features:

- Connects type-C device to four SuperSpeed USB type-A ports for additional peripherals
- USB-A ports support SuperSpeed (5Gbps) data transmission, charging up to 5V/1A
- Overcurrent protection; hot-swappable
- LED power indicator
- Plug and play
- Three-Year Warranty

Specifications:

Standards and Certifications

- USB
- FCC
- CE
- RoHS2
- WEEE

General

- Data transfer speeds: 5 Gbps

For more information on Manhattan products, consult your local dealer or visit www.manhattan-products.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

- 1 upstream port with built-in cable, standard-C male
- 4 downstream ports, standard-A female
- Up to 1A total power output
- Bus powered
- Overcurrent protection

Connections

- USB type-C, 24-pin, male
- (4) USB type-A, 4-pin, female

Physical

- 24-AWG cable gauge
- Cable Length: 20 cm (8 in.)
- Withstanding voltage: 300 VDC
- Insulation resistance: 10 MOhm
- Conductive resistance: 5 Ohm
- Housing: ABS plastic
- Dimensions: 89 x 38 x 10 mm (3.5 x 1.5 x 0.4 in.)
- Weight: 31 g (1.1 oz.)
- Shielded

Operating Environment

- Operation Temperature: 32 ~ 104°F (0 ~ 40°C)
- Storage Temperature: -4 ~ 140°F (-20 ~ 60°C)
- Humidity (noncondensing): 5 ~ 90%

System Requirements

- Windows XP/Vista/7/8.1/10 or Linux or Mac 9.x/10.x or above

Package Contents

- SuperSpeed USB 3.1 Gen 1 C Hub
- Quick Instruction Guide

