

## Cable marker label - MM-WML 3 (EX10)R C1 WH/BK - 0803931

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cable marker label, Roll, white, unlabeled, can be labeled with: THERMOFOX, Mounting type: Adhesive, Lettering field: continuous x 10 mm

### Key commercial data

|                  |               |
|------------------|---------------|
| package_quantity | 1             |
| GTIN             | 4055626212111 |

### Technical data

#### Dimensions

|                |         |
|----------------|---------|
| Length (b)     | 6.5 m   |
| Width (a)      | 18 mm   |
| Cable diameter | to 3 mm |

#### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -40 °C ... 80 °C |
|---------------------------------|------------------|

#### General

|                       |                                |
|-----------------------|--------------------------------|
| Color                 | white                          |
| Components            | Free from silicone and cadmium |
| Material              | Vinyl polymer                  |
| Wipe resistance       | DIN EN 61010-1 (VDE 0411-1)    |
| Marking mounting type | Adhesive                       |

#### Standards and Regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190219 |
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27400401 |

## Cable marker label - MM-WML 3 (EX10)R C1 WH/BK - 0803931

### Classifications

#### eCl@ss

|                   |          |
|-------------------|----------|
| <b>eCl@ss 9.0</b> | 27400401 |
|-------------------|----------|

#### ETIM

|                 |          |
|-----------------|----------|
| <b>ETIM 5.0</b> | EC001530 |
| <b>ETIM 6.0</b> | EC001530 |

#### UNSPSC

|                    |          |
|--------------------|----------|
| <b>UNSPSC 13.2</b> | 39131504 |
|--------------------|----------|

### Drawings

Phoenix Contact 2016 © - all rights reserved  
<http://www.phoenixcontact.com>