



DRY LUBE - F

Reference : 10257

1. General description

Grease and oil free lubricant for the lubrication of wooden, plastic or metal surfaces. Clean, dry and not sticky. Resistant till 250°C.

2. Features

- Particularly suitable for use in areas where a wet film lubricant cannot be used due to possible environmental dust and dirt adherence.
- Clean, dry and non-oily.
- Functional over a wide temperature range.
- Produces a very low coefficient of friction.
- High temperature resistance.
- Safe on most rubbers, plastics and coatings. Test on sensitive or stressed materials before use.

3. Applications

- Plastic drives and sliding mechanisms.
- Fine mechanics.
- Pneumatic tools.
- Precision instruments.
- Valves.
- Surface treatment.
- Particularly suitable in low load, low speed applications.

4. Directions

- Shake well before use.
- Shake until the agitator ball moves freely in the can.
- To remove residues or excess product, use one of the CRC cleaners.
- Spray from a distance of approximately 20 - 30 cm.
- Allow to dry at room temperature.
- Do not use on energized equipment.
- To remove residues or excess product, use one of the CRC cleaners.
- **A safety data sheet (MSDS) according to EC Regulation N° 1907/2006 Art.31 and amendments is available for all CRC products.**
- Based upon the present state of our knowledge and information received from our suppliers, evaluation of this



Manufactured by :
CRC Industries Europe bvba
Touwslagerstraat 1
9240 Zele Belgium
Tél.: (32)(0) 52/45.60.11 Fax : (32)(0) 52/45.00.34
www.crcind.com



**DRY LUBE - F**

Reference : 10257

product indicates that it is free from nut oils and their derivatives.

5. Typical product data (without propellant)

Appearance	Propane/butane propelled liquid.
Color	White.
Odor	Characteristic odor.
Density	0.73 g/cm ³ (@ 20°C).
Operating temperature active product	-150 to +260 °C
Solubility	Insoluble in water

6. Packaging

Aerosol 12x400 ML

All statements in this publication are based on service experience and/or laboratory testing. Because of the wide variety of equipment, conditions of use and the unpredictable human factors involved, we recommend that our products are tested on-the-job prior to use. All information is given in good faith but without warranty neither expressed nor implied. This Technical Data Sheet may already have been revised as a result of a change in legislation, availability of components or newly acquired experiences. The latest and only valid version of this Technical Data Sheet will be sent to you upon simple request or can be found on our website: www.crcind.com We recommend that you register on our website for this product, thus enabling you to automatically receive any future updates.

Version CRC_GREEN-FG_DRY_LUBE-20100204

Date 04/02/2010



Manufactured by :
CRC Industries Europe bvba
Touwslagerstraat 1
9240 Zele Belgium
Tél.: (32)(0) 52/45.60.11 Fax : (32)(0) 52/45.00.34
www.crcind.com

