

**Industrial Ethernet  
IE-FCI-HD15-FF**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 1429-0  
Fax: +49 5231 14292083  
www.weidmueller.com



FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

**General ordering data**

Type	IE-FCI-HD15-FF
Order No.	<a href="#">1556290000</a>
Version	FrontCom, VGA coupling, Signal insert VGA/HD15, Socket / socket
GTIN (EAN)	4050118369755
Qty.	1 pc(s).

**Data sheet**

**Industrial Ethernet  
IE-FCI-HD15-FF**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Net weight 9 g

**Temperatures**

Operating temperature -55 °C...105 °C      Storage temperature  
 Installation temperature

**Technical data**

Contact surface	Gold over nickel	Current-carrying capacity	3 A
Dielectric strength, contact / contact	1000 V <sub>eff</sub> / 1 min	Insulation resistance	1000 MΩ at 500 V DC
No. of poles	25		

**General data**

Insert type	Signal insert VGA/HD15	Product type	VGA coupling
Protection degree	IP20		

**Electrical properties**

Dielectric strength, contact / contact	1000 V <sub>eff</sub> / 1 min	Insulation resistance	1000 MΩ at 500 V DC
--	-------------------------------	-----------------------	---------------------

**Standards**

Certificate No. (GERMLLOYD) 13866-15

**Classifications**

ETIM 5.0	EC000456	ETIM 6.0	EC001121
UNSPSC	31-16-23-03	eClass 6.2	27-25-05-04
eClass 7.1	27-18-92-17	eClass 8.1	27-18-92-17
eClass 9.0	27-18-92-17		

**Approvals**

Approvals




ROHS Conform

**Industrial Ethernet  
IE-FCI-HD15-FF**


**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com

**Drawings**

**Dimensioned drawing**



**Dimensioned drawing**



**Dimensioned drawing**

