

WIRELESS PASSAGE DETECTOR

Infrared motion detector – with transmitter and receiver suitable for wall mounting or as tabletop unit

The wireless passage detector notifies you whenever someone has entered the monitoring area of the motion detector.

- No installation - immediately ready-to-use
- Ideal for monitoring rooms, entrances, passage ways etc.
- Radio range up to 100m (open field) – expandable with repeater (mod. CUVED CR-R1)
- Individually codable to avoid interference with similar devices in their neighbourhood
- **Expandable:** up to 8 transmitters and receivers can be used

TRANSMITTER

- Motion detector for indoor and protected outdoor areas
- Detection range up to 8 m
- All-round coverage with 140° aperture angle or focused monitoring with 3 different surveillance limiters
- 8 selectable melodies • Motion response delay adjustable 1, 10 or 20 sec.
- Motion response sensitivity 3-step adjustable
- Bell tone volume adjustable in 2 steps
- Power supply: selectively with enclosed AC adapter or with 4 x 1.5V AA batteries (not included)
- Sound selector switch: 1. Melody transmitter + receiver
2. Melody receiver only
3. Alarm tone sender + melody receiver
- Power supply: selectively with enclosed AC adapter or with 4 x 1.5V AA batteries (not included)

RECEIVER

- Visual and audible announcement (8 selectable melodies)
- Bell tone volume adjustable in 2 steps
- Low battery indicator light for transmitter and receiver
- Power supply: selectively with enclosed AC adapter or with 4 x 1.5V AA batteries (not included)



INCL. STAND

UP TO
100m
RADIO RANGE

UP TO
8m
DETECTION RANGE

8
MELODIES

VISUAL AND
AUDIBLE
ANNOUNCEMENT

EXPANDABLE

DGF-300

WIRELESS PASSAGE DETECTOR

MODEL	DGF-300 Wireless Passage Detector	Art. no: 41058
SCOPE OF DELIVERY	1x transmitter, 1x receiver, 2x AC adapter, 3x surveillance limiters, 2x stand	
DEVICE	150 x 115 x 28 mm (transmitter & receiver) w x h x d • white plastic housing	
GIFTBOX	260 x 185 x 80 mm (w x h x d) • 1.0 kg	
EXPORT BOX	5 sets • 435 x 285 x 200 mm (w x h x d) • 5.1 kg	
POWER SUPPLY	Transmitter & receiver each 4x 1.5V AA (not included) or AC adapter 6V / 100mA	
RANGE	Up to 100 meters (open field) • Frequency: 434 MHz • Detection range up to 8 meters	
APPROVAL	European Union	
EAN CODE	4250109133000	


ACCESSORY

ADDITIONAL UNITS

MODEL	DGF-300 TX Additional Transmitter	Art. no: 41059	EAN-CODE: 4250109133017
MODEL	DGF-300 RX Additional Receiver	Art. no: 41060	EAN-CODE: 4250109133024

ACCESSORY

TRANSMITTER DGF-300 TX



RECEIVER DGF-300 RX

