

- Product Data Sheet -



Article		Competition 210 lm - Headlamp	
Art. number	LX0HLA3AAA	Color	Grey/ Black
Manufacturer	LiteXpress	Material	Plastic/ Nylon
		Recom. Retail Price	19,95 €



Description: It does not matter whether the barbecue lasts late into the night or you ride your bike home in the dark, the LED headlamp LX0HLA3AAA by LiteXpress is everywhere. Regardless of the time of day or the season, it is a practical helper not only for sports activities, but also in security companies, the industry or just in the local workshop. Even with repairs on the car area, where the right illumination is important, the headlamp brings the light where it is needed. With its four light modes, it allows flexible illumination as you need it, thus providing valuable services. The special features are: Pressure switch with 'Direct Switch-Off' function, adjustable and flexible headband, lamp head can be swiveled in several stages, small-format plastic housing with red light LEDs, splash water protection according to IPX4.

Features - Insulation Products

Insulation effect		Sealing		Capacity	
Cold in hours	n/a	Type of lid	n/a	Capacity in liters	n/a
Hot in hours	n/a	Filling hole in cm	n/a		
Specials					

Features - Flashlights

Battery/Rech. Battery		Brightness		Other	
Type	AAA	Max lumens	210	Light source	LED
Amount required	3	Min lumens	60	Amount of modes	4
Weight battery in gr	11,00	Luminous range		Modes / functions	High, Direct Switch-Off, Low, Quick Flashing
Total weight in gr	33,00	Max meters	140	Special features	
Batteries included?	yes	Min meters	55		
		Lighting duration			
		Max ¹ h	45,0		
		Min ¹ h	70,0		

¹ Max relates to the lighting duration in highest light mode and Min to the duration in lowest light mode

Dimensions / Others

Inner Carton		Product		Other	
Length in cm	15,20	Length in cm	4,40	Country of Origin	China
Width in cm	18,30	Width in cm	6,50	Customs tariff num.	8513100000
Height in cm	25,60	Height in cm	3,50	EAN13 number	4895168100763
Weight in gr	1.360,00	Diameter	-		
Units	6	Weight in gr	53,00		
Outer Carton		Product packaging		Information - Multitools / Knives	
Length in cm	31,30	Length in cm	4,00	Total length in cm	n/a
Width in cm	38,00	Width in cm	13,50	Handle length in cm	n/a
Height in cm	53,80	Height in cm	24,50	Blade length in cm	n/a
Weight in gr	11.460,00	Weight in gr	140,00	Tools included	n/a
Units	48	Units	1		