

# Shrink sleeve - MM-WMS 6,4 (EX10)R C1 WH/BK - 0803925

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Shrink sleeve, continuous, cassette, white with black imprint, mounting type: slide-on, cable diameter: 2.1 - 6.4 mm, can be marked with THERMOFOX

## Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4055626212050

## Technical data

### Dimensions

<b>Length (b)</b>	1.8 m
<b>Width (a)</b>	10 mm
<b>Cable diameter</b>	2.1 mm ... 6.4 mm

### Ambient conditions

<b>Ambient temperature (operation)</b>	-55 °C ... 135 °C
--	-------------------

### General

<b>Color</b>	white
<b>Base element material</b>	polyolefine
<b>Components</b>	free from silicone, halogen, and cadmium
<b>Material</b>	Polyolefine
<b>Wipe resistance</b>	DIN EN 61010-1 (VDE 0411-1)
<b>Marking mounting type</b>	slide on

### Standards and Regulations

<b>Wipe resistance</b>	DIN EN 61010-1 (VDE 0411-1)
------------------------	-----------------------------

## Classifications

### eCl@ss

<b>eCl@ss 4.0</b>	24190219
<b>eCl@ss 4.1</b>	24190219
<b>eCl@ss 5.0</b>	27400401
<b>eCl@ss 5.1</b>	27400401
<b>eCl@ss 6.0</b>	27400401
<b>eCl@ss 7.0</b>	27400401

# Shrink sleeve - MM-WMS 6,4 (EX10)R C1 WH/BK - 0803925

## Classifications

### eCl@ss

<b>eCl@ss 8.0</b>	27400105
<b>eCl@ss 9.0</b>	27400401

### ETIM

<b>ETIM 3.0</b>	EC001530
<b>ETIM 4.0</b>	EC000217
<b>ETIM 5.0</b>	EC000217
<b>ETIM 6.0</b>	EC000217

### UNSPSC

<b>UNSPSC 6.01</b>	30211811
<b>UNSPSC 7.0901</b>	39121410
<b>UNSPSC 11</b>	39121410
<b>UNSPSC 12.01</b>	39121410
<b>UNSPSC 13.2</b>	39131504

## Drawings

Phoenix Contact 2016 © - all rights reserved  
<http://www.phoenixcontact.com>