

TALKABOUT™



MOTOROLA
SOLUTIONS



T82

WALKIE-TALKIES

CONQUER EVERY MOMENT

GO ADVENTURE

The TALKABOUT T82 is the perfect partner for your next adventure. Durable, with an IPX2 rating, the T82 can take the drops and splashes you're likely to encounter on your treks. The new hidden display comes alive when you need it and makes calling easier. The easy pairing button makes setup a breeze. A built-in LED torch provides emergency light when needed so you can read your map in the dark. And with a range of up to 10km*, the T82 will ensure you stay connected.

KEY FEATURES



PMR446 radios
- license free



Easy pairing



LED torch



Splash proof IPx2



Hidden display



16 channels plus 121
privacy codes**

UP TO
10
KM RANGE*



TALKABOUT™

T82

WALKIE-TALKIES

GO **ADVENTURE**



GENERAL

Model: Talkabout T82
Colour: Orange & Black
Frequency Band: PMR446
Tx Power: 500mW
Bandwidth: 12.5Khz
Channels: 16 +121 privacy codes**
Weight: 197 grams (with belt clip and battery)
Range: Up to 10km*
Size WxDxH: 5.7 x 18.1 x 3.3 cm

PACKAGE CONTENTS

2 walkie-talkies
2 belt clips
Mains charger with 2 micro USB plugs
2 NiMH rechargeable battery packs
Personalization stickers (16pcs)
Instruction manual

FEATURES

Hidden display
LED torch
Channel scan
VOX
Auto squelch
Channel monitor
Emergency alert button
Easy pairing
Dual channel monitor

TO LEARN MORE, VISIT US ON THE WEB AT

motorolasolutions.com/talkabout

LIKE US ON FACEBOOK

facebook.com/MotorolaTalkaboutWalkieTalkies

TALKABOUT T82 Twin Pack & Chgr UK: B8P00810EDRMAW
TALKABOUT T82 Twin Pack & Chgr WE: B8P00811EDRMAW

*Subject to terrain and conditions.

**Restricted to 8 channels in Russia by law. Please refer to user guide.

***Based on standard usage of 5/5/90 cycle.

MOTOROLA, MOTOROLA SOLUTIONS and the Stylized M Logo are trademarks or registered trademarks of Motorola Trademark Holdings, LLC and are used under license. All other trademarks are the property of their respective owners. © 2017 Motorola Solutions, Inc. All rights reserved.



MOTOROLA
SOLUTIONS



SKIING



HIKING



BIKING



CLIMBING



SNOW BOARDING

MECHANICAL

Keypad lock
Battery level indicator
Belt clip
Micro USB port for charging
2.5 mm headset jack
Splash proof IPX2

ALERTS

20 call tones
Vibrate alert
Keypad tones
Talk confirmation tone/Roger beep

POWER

Rechargeable NiMH pack (included)
Compatible with standard AA-sized batteries


BATTERY LIFE

NiMH 800 mAh (included) - up to 18 hours***
NiMH 1300 mAh high capacity (optional) - up to 26 hours***

CHARGING

Micro USB charger (included)
Compatible with drop-in charging dock (sold separately)

PACKAGE CONTENTS



MOTOROLA, MOTOROLA SOLUTIONS and the Stylized M Logo are trademarks or registered trademarks of Motorola Trademark Holdings, LLC and are used under license. All other trademarks are the property of their respective owners. © 2017 Motorola Solutions, Inc. All rights reserved.