





RoHS & REACH Compliant

| | | | |
|-----------|------------------|------|------|
| Signature | Revision History | Date | Rev. |
|-----------|------------------|------|------|





DISPLAYPORT MALE
INS:BLACK




PCB TOP



PCB BOTTOM



Printing color:White



Printing color:White

LABEL :BLACK BASE WHITE WORDS



WW : week
YY : year(2016=16)

NOTE:

- CABLE:UL20276 [32AWG(7/0.08T.C)×1P INS:FOAM-PE+D.W(7/0.08T.C)+AL/MY+Mylar]×5C+32AWG(7/0.08T.C)×4C+28AWG(7/0.12B.C)×1C+AL/MY+BRAID(85%T.C) PVC JACKET OD:5.2±0.2mm COLOR:BLACK .
- CONNECTOR:
P1:DISPLAYPORT 20P MALE W/LATCH CONTACT:3u";SHELL:GOLD FLASH PLATED .
P2:HDMI A TYPE FEMALE CONTACT:3u";SHELL:GOLD PLATED .
- SHIELD:P1 COPPER-FOIL POINT SOLDERED TO CONNECTOR SHELL&CABLE BRAID .
- HOOD:P1&P2 ASS'Y TYPE,PLASTIC HOOD COLOR:BLACK .
SR:MOLDED TYPE,PVC 45P,COLOR:BLACK .
- IC TYPE: PTN3361B .
- TEST REQUEST:100% Computer TEST .
(1)Resolution:1920×1080P .
- PACKING:EACH PC / POLYBAG(Size:L160×W110×0.05mm) + Specification .

| | | | | | |
|-----------------------------------|--------------|---------|---|-----|-------|
| | Date | Name | Part No. | | |
| Drawn by | 2017/07/3 | Cheng/F | AK-340400-001-S | | |
| Checked by | 2017/07/3 | Alex | EAN:4016032289241 | | |
| Approved by | 14July, 2017 | Joe | Title | | |
| ASSMANN Electronic GmbH | | | DISPLAYPORT/M TO HDMI/F CONVERTER(1.2V) | | |
| | | | Scale | N/A | Sheet |
| | | | Unit | MM | 1/3 |

RoHS & REACH Compliant

Specification Size: 68 x 78mm ;黑白印刷

NON-WIRELESS PRODUCT

Klasse B Gerät ohne Netzteil

English:
 Hereby ASSMANN Electronic GmbH, declares that this device is in compliance with the requirements of Directive 2014/30/EU and the Directive 2011/65/EU for RoHS compliance. The complete declaration of conformity can be requested by post under the below mentioned manufacturer address.

Assmann Electronic GmbH
 Auf dem Schüffel 3
 58513 Lüdenscheid
 Germany

Warning:
 This device is a class B product. This equipment may cause some radio interference in living environment. In this case, the user can be requested to undertake appropriate measures to prevent interference.

German:
 Hiermit erklärt die ASSMANN Electronic GmbH, das der Artikel in Übereinstimmung mit den Anforderung und Vorschriften der Richtlinien 2014/30/EU und RoHS 2011/65/EU befindet. Die vollständige Konformitätserklärung können Sie postalisch unter der unten genannten Herstelleradresse anfordern.






Assmann Electronic GmbH
 Auf dem Schüffel 3
 58513 Lüdenscheid
 Germany

Warning:
 Dies ist eine Einrichtung der Klasse B. Diese Einrichtung kann im Wohnbereich Funkstörungen verursachen. In diesem Fall kann vom Betreiber verlangt werden, angemessene Maßnahmen durchzuführen.

French:
 La ASSMANN Electronic GmbH, déclare par les présentes, que cet appareil est en conformité avec les exigences de la Directive 2014/30/EU et avec celles de la Directive 2011/65/EU sur la conformité RoHS. La déclaration de conformité complète peut être demandée par courrier à l'adresse du fabricant mentionnée ci-dessous.

Assmann Electronic GmbH
 Auf dem Schüffel 3
 58513 Lüdenscheid
 Germany

Avertissement:
 Ce dispositif appartient à la classe B. Ce dispositif est susceptible de provoquer des perturbations radio-électriques dans une zone habitable. Il peut être exigé à l'utilisateur de prendre des mesures appropriées.

| | | | |
|-----------------------------------|--------------|---------|---|
| | Date | Name | Part No. |
| Drawn by | 2017/07/3 | Cheng/F | AK-340400-001-S |
| Checked by | 2017/07/3 | Alex | EAN:4016032289241 |
| Approved by | 14July, 2017 | Joe | |
| ASSMANN Electronic GmbH | | | Title |
| | | | DISPLAYPORT/M TO HDMI/F CONVERTER(1.2V) |
| Scale | N/A | Sheet | |
| Unit | MM | | 2/3 |

| | | | |
|-----------|------------------|------|------|
| Signature | Revision History | Date | Rev. |
|-----------|------------------|------|------|

Package Details

RoHS & REACH Compliant

| | | | |
|-----------|------------------|------|------|
| Signature | Revision History | Date | Rev. |
|-----------|------------------|------|------|

Single Cable


| P/N | Cable Length | Rolling Size (Single Cable) | PACKING (Single Cable) | Box Size (Single Cable) | Article Weight (Single Cable) |
|-----------------|--------------|-----------------------------|------------------------|-------------------------|-------------------------------|
| AK-340400-001-S | 0.15M | MM MAX | Ordinary Polybag | 160×110×0.05mm | 0.0262Kg |

Inner Packing Unit

| P/N | Cable Length | Quantity (Inner Packing Unit) | Type (Inner Packing Unit) | Size (Inner Packing Unit) | Weight (Inner Packing Unit) |
|-----------------|--------------|-------------------------------|---------------------------|---------------------------|-----------------------------|
| AK-340400-001-S | 0.15M | 10pcs | Ordinary Polybag | 12.0"×14.0"×0.05mm | 0.272Kg |

CARTON DETAILS

| P/N | Cable Length | Quantity (Carton) | Measurement (Carton) | N.W. (Carton) | G.W. (Carton) |
|-----------------|--------------|-------------------|-----------------------|---------------|---------------|
| AK-340400-001-S | 0.15M | 200pcs | L381×W302×H241mm(K=K) | 5.24Kg | 6.2Kg |



| | | | |
|-----------------------------------|--------------|---------|---|
| | Date | Name | Part No. |
| Drawn by | 2017/07/3 | Cheng/F | AK-340400-001-S |
| Checked by | 2017/07/3 | Alex | EAN:4016032289241 |
| Approved by | 14July, 2017 | Joe | |
| ASSMANN Electronic GmbH | | | Title |
| | | | DISPLAYPORT/M TO HDMI/F CONVERTER(1.2V) |
| | | | Scale Unit |

- × "ROTTERDAM" is for Sea Freight shipment
- × "COLOGNE" is for Air Freight shipment
- × "LUDENSCHIED" is for Fedex or UPS shipment