

Floe Riing RGB 360 TT Premium Edition

P/N: CL-W158-PL12SW-A

Floe Riing RGB 360 TT Premium Edition

• Features

- Digital control addressable LEDs ring on water block and fans
- 16.8 million color RGB spectrum
- Top of the line liquid cooler, equipped with power and performance. No Refills Needed.
- High static pressure design for radiator cooling
- Universal Socket Compatibility



Release the full CPU Horsepower



• Specification

Compatibility(CPU Socket)		Intel LGA 2066/2011-3/2011/1366/1156/1155/1151/1150 AMD AM4/FM2/FM1/AM3+/AM3/AM2+/AM2
Water Block	Material	Copper
Pump	Rated Voltage	12 V/ 5V
	Rated Current	0.325 A / 0.4A
	Motor Speed	3600 R.P.M
Fan	Dimension	120 x 120 x 25 mm
	Speed	500~1400RPM
	Noise Level	19.8 ~ 24.7 dB-A
	Rated Voltage	12 V
	Max. Air Flow	14.2~42.34 CFM
	Max. Pressure	0.17~1.54 mm-H2O
	Connector	5 pin
Radiator	Dimension	360 x 120 x 27 mm
Tube	Length	326 mm
	Material	Rubber
Weight		1610g

Floe Riing RGB 360 TT Premium Edition

• Detailed Features :

- Digital control addressable LEDs ring on water block and fans
- 16.8 million color RGB spectrum
- High performance copper base plate accelerates the heat conductivity.
- High static pressure design for radiator cooling
- High reliability low profile pump provides quick liquid circulation.
- Low evaporation tube decreases the loss of coolant effectively.
- 360mm radiator maximizes the surface for best cooling power.
- Universal Socket Compatibility

Intel: LGA2066, LGA2011-3, LGA2011, LGA1366, LGA1156/1155/1151/1150

AMD: AM4, FM2, FM1, AM3+, AM3, AM2+, AM2

• Appearance



High Performance Water block



High Reliability Pump



Powerful Cooling Fan

Floe Riing RGB 360 TT Premium Edition

• Appearance



High Efficiency Radiator



Customized LED lighting effect



Universal Socket Compatible



Controller



Application

Floe Riing RGB 360 TT Premium Edition

• Appearance



RGB Spectrum Mode:

A gorgeous and seamless transition through the entire range of 16.8 million RGB colors



Ripple Mode:

RGB Colors ripple out across the fan



Flow Mode:

RGB or Single color flow in a clockwise direction



Pulse Mode:

A slow fade in and fade out of your color choice

Floe Riing RGB 360 TT Premium Edition

Floe Riing RGB 360


TT Premium Edition

Release the full CPU Horsepower

• Application



• Performance



Tt Thermaltake
COOL ALL YOUR LIFE

Floe Riing RGB 360 TT Premium Edition

P/N: CL-W158-PL12SW-A

Floe Riing RGB 360

TT Premium Edition

Release the full CPU Horsepower



Support
AM4
LGA 2066

 **Thermaltake**
COOL all YOUR LIFE