

Wireless Presentation Laser Pointer Télécommande de Présentation Sans-fil avec Pointeur Laser Schnurloser Presenter mit Laserpointer Telecomando senza fili per presentazioni con Puntatore Laser Mando Inalámbrico para Presentaciones con Puntero Láser

LP200B

August International Ltd United Kingdom Telephone: +44 (0) 845 250 0586 Email: service@augustint.com Web: www.augustint.com

User Manual

1. Introduction

This wireless presenter is designed to control your computer during presentations. It gives you the freedom to speak without having to stand by your computer or relying on an assistant. Simple to use, just plug and play, no driver required.

The device enables you to control your computer wirelessly from up to 15 meters (48 feet) away, using a Radio Frequency (RF) transmitter that doesn't require line of sight to your PC. With its in-built laser pointer, the LP200 is the ideal tool for presentations, teaching, meetings, speeches, training etc.

2. Main Features

- Plug and Play for Computer Power Point Presentation
- Remote Page Changer and Shortcut Keys
- Integrated Red Laser Pointer
- Internal Storage for USB Signal Receiver
- Remote Control Range: up to 15m
- Compatible with Windows 8, 7, Vista, XP, 2000,98, Mac OS & Linux

3. Parts & Functions



- 1. Laser
- 2. Page Up
- 3. Page Down
- 4. Start / End Slide Show
- 5. Slide Show Screen On / Off
- 6. Close Window
- 7. Application Switcher (ALT+TAB)
- 8. Battery Compartment
- 9. USB Receiver

4. Battery Installation

- The unit is powered by 1 x CR2032 battery.
- Use a coin to unlock the battery compartment cover and remove it.







Replace the battery compartment cover and use a coin to lock it.



Note:

- 1) Always follow polarity instructions when inserting the battery.
- 2) Remove spent batteries from presenter immediately.
- Remove battery when not in use to prevent possible damage from battery corrosion.
- 4) If the presenter does not function correctly or if the operating range is reduced, please try replacing the battery.

5. Specifications

Presenter	
Technology	Radio Frequency
Frequency	2.4GHz
Operating range	Up to 15m
Laser range	Up to 200m
Power supply	1 x CR2032 battery
Operating voltage	2.4 – 3V
Laser wavelength	650nm
Laser power	<1mW
Dimensions	102 x 30 x 9mm
Weight	18g

USB Receiver	
Operating systems	Windows 98 / 2000 / XP / Vista / 7 / 8, Linux and Mac OS
USB version	USB 1.1 compatible with USB 2.0 and USB 3.0
Work voltage	4.5 - 5V
Dimension	22x14.5x5.7mm
Weight	2g

Warning:

Laser radiation Class 2 laser product Do not view directly with optical instruments Do not point at people and animals Please keep out of reach of children

Note:

Please note, these instructions are only intended for reference. August International Ltd reserves rights to revise the product specifications, features and design without notice.