

**THM  
EL 12 MM GN 30M**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com


**Customised identification: EL**

The endless variations of MultiMark markers make them an economical alternative to conventional tag rails or special labels. For any given width, the length can be precisely configured by the software to match the respective markers perfectly. A blade is used to cut the labels individually to the specified size. Perfect for producing large labels for function blocks or complete terminal blocks.

**Your benefits with MultiMark**

- Double laminated polyester
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

**General ordering data**

Type	EL 12 MM GN 30M
Order No.	<a href="#">2528320000</a>
Version	THM, Device markers, 12, green
GTIN (EAN)	4050118539219
Qty.	1 pc(s).
compatible printer	<a href="#">2448870000</a> <a href="#">2430920000</a>

## Data sheet

**THM  
EL 12 MM GN 30M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technical data

### Dimensions and weights

Length	30,000 mm	Length (inches)	1,181.1 inch
Height	12 mm	Height (inches)	0.472 inch
Depth	0.1 mm	Depth (inches)	0.004 inch
Net weight	107 g		

### General data

Adhesive	Acrylate adhesive	Approval acc. to UL 969	Yes
Colour	green	Halogen	No
Length	30,000 mm	Material	Polyester
Number per roll	1	Operating temperature range	-40...120 °C
UL 94 flammability rating	V-0	Version	halogen-free, Self-adhesive

### Classifications

ETIM 6.0	EC001288	eClass 6.2	27-14-91-29
eClass 9.0	27-40-06-29	eClass 9.1	27-40-06-29

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">EPLAN</a>
------------------	-----------------------

**Data sheet**

**THM  
EL 12 MM GN 30M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

