SIEMENS

## Data sheet 8MF6026-4R

Standard cabinet 8MF6 HxWxD=2000x 1200x 600 Installation: Side-by-side non-ventilated, assembled, welded IP40

Figure similar

| Model | |
|---|---|
| Product brand name | SIVACON |
| Product designation | standard system cubicle |
| Type of installation | installation as suite |
| Design of the surface | powder-coated |
| Design of the product / EMC version | No |
| Design of the control cabinet / PC design | No |
| Design of the control cabinet / Console design | No |

| Protection class | |
|---|---|
| Protection class IP | IP40 |
| Suitability for installation | |
| • for inch dimensions | 10-inch, 17-inch, 19-inch, 21-inch, 23-inch, 24-inch |
| • for metric dimensions | M8 |
| Suitability for use / for outside use | No |

| Appearance | |
|---|---|
| RAL color number | RAL 7032 |
| Color | pebble grey |


Subject to change without notice
© Copyright Siemens

| | |
|---|---|
| Product component | |
| • removable frame | No |
| • Ventilation door | No |
| • Mounting plate | No |
| • Rear door | No |
| • pitched roof | No |
| • Viewing door | No |
| • height-adjustable mounting plate | No |
| Number of locking devices | 1 |
| Number of doors | 2 |

## Mechanical Design

| | |
|---|---|
| Height | 2 000 mm |
| Width | 1 200 mm |
| Depth | 600 mm |
| Number of modular height units / for installation height | 38 |
| Mounting type | standing |
| Mounting type / 19-inch installation | Yes |
| Net weight | 155 kg |
| Material | steel |

## Certificates

| | |
|---|---|
| Reference code | |
| • acc. to DIN EN 61346-2 | U |

| General Product Approval | Declaration of Conformity | other |
|---|---|---|
| EAC | CE EG-Konf. | Miscellaneous |

## Further information

**Information- and Downloadcenter (Catalogs, Brochures,…)**
http://www.siemens.com/lowvoltage/catalogs

**Industry Mall (Online ordering system)**
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF6026-4R

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**
https://support.industry.siemens.com/cs/ww/en/ps/8MF6026-4R

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**
http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF6026-4R

**CAx-Online-Generator**
http://www.siemens.com/cax

**Tender specifications**
http://www.siemens.com/specifications


Subject to change without notice
© Copyright Siemens

Subject to change without notice
© Copyright Siemens