

SIVACON, Control panel Empty enclosure, without side panels, according to IEC 62208, IP55, H: 2200 mm, W: 1200 mm, T: 400 mm



| Model | |
|--|---------------------------------|
| Product brand name | SIVACON |
| Product designation | Empty control cabinet enclosure |
| Design of the product | according to IEC 62208 |
| Design of the surface | Powder-coated |
| Design of the product / EMC version | No |
| Protection class | |
| Protection class IP | IP55 |
| Operating resource protection class | Safety class 1 |
| Suitability | |
| Suitability for installation / for metric dimensions | Yes |
| Suitability for integration | |
| • surface-mounted installation | Yes |
| • flush mounting | No |
| Suitability for use / for outside use | No |
| Appearance | |
| RAL color number | RAL 7035 |
| Color | light grey |

Product details

| | |
|--|-----|
| Product component | |
| • Ventilation door | No |
| • Mounting plate | Yes |
| • Rear door | No |
| • Viewing door | No |
| • height-adjustable mounting plate | Yes |
| Product feature / of the enclosure / housing for side-by-side mounting | Yes |

Number

| | |
|---------------------------|---|
| Number of locking devices | 0 |
| Number of doors | 2 |

Mechanical Design

| | |
|------------------------|-----------|
| Height | 2 200 mm |
| Width | 1 200 mm |
| Depth | 400 mm |
| Mounting type | |
| • 19-inch installation | No |
| • floor mounting | Yes |
| • wall mounting | No |
| Net weight | 183.22 kg |
| Material | steel |

Certificates

| | |
|--------------------------|----|
| Reference code | |
| • acc. to DIN EN 61346-2 | U |
| • acc. to DIN EN 81346-2 | UC |

| | | | |
|---------------------------------|----------------------------------|--------------------------|--------------|
| General Product Approval | Declaration of Conformity | Test Certificates | other |
|---------------------------------|----------------------------------|--------------------------|--------------|



[Special Test Certificate](#)

[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF1224-3BR5>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MF1224-3BR5>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF1224-3BR5



