

DIGITUS® USB-C Docking Stations



Part number	DA-70860	DA-70862	DA-70861	DA-70863	DA-70864	DA-70865
Product name	12" Universal Docking Station USB Type-C™		Universal Docking Station USB Type-C™			Universal Travel Docking Station USB Type-C™
Number of connections	11	11	11	11	13	9
Dock type	On-Top Dock	On-Top Dock	Side Dock			
HDMI port	✓	✓	✓	✓	✓	✓
VGA port	✓	✓	✓	✓	✓	✓
Mini DisplayPort port	✓	✓	✓	✓	✗	✗
DisplayPort port	✗	✗	✗	✗	✓	✗
USB 3.0 port	3x	3x	3x	3x	4x	2x
USB Type-C™ port (PD)	✓	✓	✓	✓	✓	✓
USB Type-C™ port (Data)	✗	✗	✗	✗	✓	✓
Audio jack (3.5 mm)	✓	✓	✓	✓	2x	✗
MicroSD card reader	✓	✓	✓	✓	✗	✓
SDHC, SDXC, MMC card reader	✓	✓	✓	✓	✗	✓
Gigabit Ethernet port	✓	✓	✓	✓	✓	✓
Power Delivery (PD) 2.0	✓	✓	✓	✓	✓	✓
Input power	60W (20V/3A)	60W (20V/3A)	60W (20V/3A)	60W (20V/3A)	100W (20V/5A)	100W (20V/5A)
UHD 4K2K / 30Hz	✓	✓	✓	✓	✓	✓
Charging function for mobile devices (BC 1.2)	✓	✓	✓	✓	2x	2x
Optional external power supply	✗	✗	✗	✗	✓	✗
Housing	Aluminium	Aluminium	Aluminium	Aluminium	Aluminium	ABS Plastic
Cable length	10.0 cm	10.0 cm	10.0 cm	10.0 cm	1.0 m, detachable	10.0 cm
Dimensions	7.5 x 28.0 x 1.5 cm (LxWxH)	7.5 x 28.0 x 1.5 cm (LxWxH)	7.5 x 13.5 x 1.7 cm (LxWxH)	12.0 x 12.0 x 1.7 cm (LxWxH)	19.5 x 8.5 x 2.2 cm (LxWxH)	12.2 x 7.0 x 1.4 cm (LxWxH)
Weight	320 g	320 g	250 g	230 g	425 g	90 g
Color	silver	grey	silver	silver	silver	black

All brand names and logos that are mentioned are trademarks or registered trademarks of the respective owners. The right to make design-related variations from the photos, mistakes and technical changes is reserved. All information is provided without guarantee. We assume no liability for printing errors. The right to delivery is reserved and subject to availability. Published by ASSMANN Electronic GmbH, Auf dem Schüffel 3, 58513 Lüdenscheid - Germany. 01/2018