

# ***Thermaltake Versa H27 TG Middle tower***

- **Style : Simple**

- **Size : Middle tower support up to ATX MB**

- **Material : Steel & Plastic & Tempered Glass**

- ***Main Feature***

- **Connection : Top-Front I/O ports with 2 x USB 3.0 and 2 x USB 2.0**

- **Ventilation : 1 preinstalled 120mm fan**

- **Support : LCS Cooling & Advance Cable Management**



# Thermaltake Versa H27 TG Middle tower

## •Specification

<b>Model</b>	<b>Versa H27 TG</b>
<b>P/N</b>	CA-1J6-00M1WN-00
<b>Case Type</b>	Middle tower
<b>Chassis Dimension (H*W*D)</b>	469 x 219 x 493 mm (18.5 x 8.6 x 19.4 inch)
<b>Net Weight(Case)</b>	7.1 kg / 15.6 lb
<b>Side Panel</b>	4mm Tempered Glass x 1
<b>Color</b>	Exterior & Interior : Black
<b>Material</b>	SPCC
<b>Cooling System</b>	<b>Rear (exhaust) :</b> 120 x 120 x 25 mm fan (1000rpm, 16dBA)
<b>Drive Bays</b>	
-Accessible	-
-Hidden	2 x 2.5" or 3.5" ; 3 x 2.5"
<b>Expansion Slots</b>	7
<b>Motherboards</b>	6.7" x 6.7" (Mini ITX), 9.6" x 9.6" (Micro ATX), 12" x 9.6" (ATX)
<b>I/O Port</b>	USB 3.0 x 2, USB 2.0 x 2, HD Audio x 1
<b>PSU</b>	Standard PS2 PSU <b>(optional)</b>
<b>Fan Support</b>	<b>Front:</b> 3 x 120mm <b>Top:</b> 3 x 120mm, 2 x 140mm <b>Rear:</b> 1 x 120mm
<b>Radiator Support</b>	<b>Front:</b> 1 x 360mm <b>Top:</b> 1 x 360mm, 1 x 280mm <b>Rear:</b> 1 x 120mm
<b>Clearance</b>	CPU cooler height limitation: <b>160mm</b> VGA length limitation: <b>310mm</b> PSU length limitation: <b>220mm</b>

# Thermaltake Versa H27 TG Middle tower

## •Packaging



Package Information	Versa H27 TG
EAN Code	4711246871304
UPC Code	841163001301
N.W	7.1 kg / 15.6 lb
G.W	8.9 kg / 19.62 lb
Carton Size (L x W x H)	555 x 305 x 552 mm (21.9 x 12 x 21.7 inch)
Cuft	3.3
Container	W/O pallet
20'	315
40'	630
40' HQ	710

# Thermaltake Versa H27 TG Middle tower

Appearance - CA-1J6-00M1WN-00



Angle view



Left Side view



Front view



Right Side view



Internal Structure



Rear view



Top view



Bottom view

# Thermaltake Versa H27 TG Middle tower

- The Cooling System – Liquid Cooling (Optional)



## **A** CPU Air Cooling System

① Rear (exhaust) : 120 x 120 x 25 mm Turbo fan x 1 (1000rpm, 16dBA)

## **B** HDD Air Cooling System(Optional)

① Front (intake) : 120 x 120 x 25 mm Turbo fan x 2 (1000rpm, 16dBA)

# Thermaltake Versa H27 TG Middle tower

## • Compatibility List

Fan Compatibility List			
	120mm	140mm	200mm
Front	3	-	-
Top	3	2	-
Rear	1	-	-

Thermaltake Compatible Fan			
	120mm	140mm	200mm
PURE FAN Series	●	●	-
LUNA FAN Series	●	●	-
Riing FAN Series	●	●	-

Radiator Compatibility List						
	120mm	240mm	360mm	140mm	280mm	420mm
Front	●	●	●	-	-	-
Top	●	●	●	●	●	-
Rear	●	-	-	-	-	-

## All-in-One Compatibility List (Water 3.0 and Floe series)

	Performer	Pro	240 Series	360 Series	140 Series	280 Series
Front	●	●	●	●	-	-
Top	●	●	●	●	●	●
Rear	●	●	-	-	-	-