



IDEAL NETWORKS

# SignalTEK NT






Quick Reference Guide  
156866 Issue 3

© IDEAL INDUSTRIES Networks Ltd 2018

A subsidiary of IDEAL INDUSTRIES INC.



IDEAL INDUSTRIES, INC.



1	RJ45 Port	13	Power module
2	RJ45 activity LED	14	Charger LED
3	RJ45 link LED	15	DC in connector
4	Optical port (SFP)	16	Autotest button
5	Optical activity LED	17	Link LED
6	Optical link LED	18	Status LED
7	USB port	19	1000 Mb/s line rate LED
8	Touchscreen display	20	100 Mb/s line rate LED
9	Function keys F1 to F3	21	10 Mb/s line rate LED
10	Escape key	22	Remote Autotest button
11	Cursor and ENTER keys	23	Power LED
12	ON/OFF button	24	Wi-Fi Adapter

Charger LED	Status
Green	Power module is charging
Off (with charger connected)	Power module is charged
Green flashing	Power module is not being charged

## Four Ways to Navigate


A



B



C







Escape - returns to previous screen  
ENTER - accepts selection






D





# Wiremap Testing



# Cable Testing



# IP Testing



## Performance Testing


2/5000 Myjob 14:43

1000 Mb/s-FD  
Auto Neg On  
No-PoE

IPv4-172.20.20.17  
IPv6- 2001:777:0db8:2::1/64

JOBs TESTS

DETECT PORTS SETUP



DATA

VOIP

RUN

TESTS

DATA

VOIP

VoIP Myjob 11:13

PASSED 00:00:10

Link Rate 1000 Mb/s-FD

Frame Size 218

IR (Mb/s) 0.9

Tx 5,160

100%

Rx 5,160

100%

Error 0

0%

RUN SAVE SETUP

VoIP Myjob 14:54

No. of Calls 10

Info. Rate (Mb/s) 0.9

Threshold (Frames) 0

Duration 00:00:10

(hh:mm:ss)

Frame Size 218

Frame Fill Random


APPLY



## Save and View Test Results



2 tests saved.  
Memory  
capacity =  
5000 tests.



Saves result to  
SignalTEK NT



View



Select Job

Select Result

OR  
Save to  
USB

TO USB

OR Smartphone  
downloads reports using  
**IDEAL AnyWARE™**  
app. for Android™ /  
Apple




Apple is a trademark of Apple Inc., registered in the U.S. and other countries.


Android is a trademark of Google Inc.

# Tests Menu Maps



## Cable Mode





## Ethernet Modes



1



2



3

