

DIAZED fuse link 690 V for cable and line protection Operating class gG Size DIII, E33, 35A



Model	
Product brand name	SETRON
Product designation	DIAZED fuse
Design of the product	For cable and line protection
Design of the fuse link	DIAZED fuse links
General technical data	
Tripping characteristic class	Other
Size of fuse system / acc. to DIN EN 60269-1	DIII
Operating class of the fuse link	gG
Diken-export / Let-through current circuit-breaker / Design	DS_5SD_DIII_690_gG_35 5SD8
Supply voltage	
Current / at AC / rated value	35 A
Supply voltage	600 V
• at DC	
Protection class	
Protection class IP	IP20, with connected conductors

Switching capacity

Switching capacity current

- | | |
|---|-------|
| • at DC / acc. to IEC 60947-2 / rated value | 8 kA |
| • acc. to IEC 60947-2 / rated value | 50 kA |

Dissipation

Power loss [W]	3.1 W
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	3.1 W

Current

Tripping residual / rated value / derated current / at 40 Cel	33.25 A
Diken-export / Let-through energy	DE_5SD_DIII_690_gG_35

Appearance

Color coding of the fuse link	black
-------------------------------	-------

Product details

Product description	Using screw adapter or adapter sleeves
---------------------	--

Mechanical Design

Mounting position	Any, preferably vertical
Net weight	73 g

Environmental conditions

Ambient temperature	-5 ... +40 °C
• during storage	Air humidity 90% at 20 °C
Environmental category	Up to 45°C at 95 % rel. humidity

Certificates

Reference code	
• acc. to DIN EN 61346-2	F
• acc. to DIN EN 81346-2	F

Declaration of Conformity

Test Certificates

other



EG-Konf.

[Type Test Certificates/Test Report](#)

[Environmental Confirmations](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SD8035>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SD8035>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)
http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SD8035

CAX-Online-Generator
<http://www.siemens.com/cax>

Tender specifications
<http://www.siemens.com/specifications>

