


## Product information

### 0975 254 101 - 0975 254 101/5 M

Industrial Connecting Solutions:I/O Modules:I/O Modules Activ - Stand Alone:Profibus:Accessories:Profibus Data Cables:Overmolded Double Ended Cordsets:0975 254 101

[http://e-catalog.hirschmann.com/link/57078-24228-255441-219791-219793-219798-220052-221142-221141/en/0975\\_254\\_101\\_0500/ui/istate](http://e-catalog.hirschmann.com/link/57078-24228-255441-219791-219793-219798-220052-221142-221141/en/0975_254_101_0500/ui/istate)

<b>Name</b>	0975 254 101
	
	Profibus signal cable, molded on both sides with M12 male connector and M12 female connector, 5 poles, B coding, 5 meter, PUR jacket, halogen free, violet.
<b>Delivery informations</b>	
<b>Availability</b>	available
<b>Product description</b>	
<b>Type</b>	0975 254 101/5 M
<b>Order No.</b>	11019
<b>Description</b>	Profibus signal cable, molded on both sides with M12 male connector and M12 female connector, 5 poles, B coding, 5 meter, PUR jacket, halogen free, violet.
<b>Note</b>	The application of these products in harsh environments should always be checked before use.
<b>Color of housing</b>	black
<b>Product characteristics</b>	Oil resistance, Drag chains, EMC resistance
<b>Classification</b>	
<b>Belden class</b>	Signal Cable
<b>Belden brand</b>	Lumberg-Automation
<b>Approvals</b>	
<b>Approvals</b>	UL
<b>Cable</b>	
<b>Cable length</b>	5 m
<b>Cable number</b>	254
<b>Cable description</b>	Bus cable Profibus
<b>Color of jacket</b>	violet
<b>Material of outer jacket</b>	PUR
<b>Without halogens as in EN 50267-2-3</b>	✓
<b>shielded</b>	✓
<b>welding spark proof</b>	✗
<b>Outer diameter of the cable</b>	7.6 mm
<b>Number of conductors</b>	2
<b>Cable design</b>	2 x 0.38 mm <sup>2</sup>
<b>Conductor design</b>	19 x 0.15 mm
<b>Flame resistant according to standard</b>	IEC 60332-2, CSA FT-2

**Belden Deutschland GmbH**  
 Im Gewerbepark 2  
 58579 Schalksmühle  
 Germany  
 Phone: +49 7127/14-1806  
 E-Mail: icos-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.