

FF 22 55/230V BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Similar to illustration

The filter fans combine a safe and profitable cabinet cooling due to their low energy consumption by maximum air flow. The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats.

General ordering data

| | |
|------------|---------------------------------------|
| Type | FF 22 55/230V BK |
| Order No. | 2556650000 |
| Version | Filter fan, 230 V, 230 V, IP55, black |
| GTIN (EAN) | 4050118567274 |
| Qty. | 1 pc(s). |

FF 22 55/230V BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Width | 145 mm | Width (inches) | 5.709 inch |
| Height | 145 mm | Height (inches) | 5.709 inch |
| Depth | 70 mm | Depth (inches) | 2.756 inch |
| Net weight | 700 g | | |

General data

| | | | |
|---------------------------------|----------|---------------------------|----------------------|
| EMC version | No | Filter class | G 4 |
| Height of installation cut-outs | 125 mm | Mounting depth | 70 mm |
| Mounting height | 5 mm | Noise emission | 44 dB (A) |
| Rated AC voltage | 230 V AC | Supply voltage, max | 230 V |
| Supply voltage, min. | 230 V | Type of connection | Terminal strip |
| Type of mounting | Snap-on | Volume flow, free-blowing | 56 m ³ /h |
| Width of installation cut-outs | 125 mm | With filter | Yes |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 6.0 | EC000320 | eClass 6.2 | 27-18-07-16 |
| eClass 9.1 | 27-18-07-16 | | |

Approvals

Approvals



ROHS

Conform

Downloads


| | |
|---|--|
| Approval/Certificate/Document of Conformity | EU Declaration of Conformity |
| Engineering Data | STEP |

FF 22 55/230V BK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Drawings

Graph



Graph

