

ALPHA 630, Floor-mounted cabinet, with open side wall, IP55,  
Protection class 1, H: 1950 mm, W: 800 mm, T: 250 mm, RAL 7035



| Model  |                       |
|--|-----------------------|
| Product brand name                                   | ALPHA 630             |
| Product designation                                  | Free-standing cabinet |
| Design of the product                                | With open side panel  |
| Surface processing                                   | powder-coated         |
| Protection class                                     |                       |
| Protection class IP                                  | IP55                  |
| Suitability for interaction / lightning protection   | Yes                   |
| Suitability for use / for outside use                | No                    |
| Appearance   |                       |
| RAL color number                                     | RAL 7035              |
| Product component                                    |                       |
| • cable entry  | Yes                   |
| • Mounting plate                                     | No                    |
| Product extension / optional / Side-by-side mounting | Yes                   |
| Mechanical Design                                    |                       |
| Height   | 1 950 mm              |
| Width  | 800 mm                |

|                             |         |
|-----------------------------|---------|
| Depth                       | 250 mm  |
| Installation depth          | 250 mm  |
| Net weight                  | 46.5 kg |
| Material / of the enclosure | Steel   |

## Certificates

### Reference code

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

U

UC

| General Product Approval | Declaration of Conformity | Test Certificates |
|--------------------------|---------------------------|-------------------|
|--------------------------|---------------------------|-------------------|



[Miscellaneous](#)



EG-Konf.

[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

## other

[Miscellaneous](#)

## Further information

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8GK1323-8KP33>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8GK1323-8KP33>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8GK1323-8KP33](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1323-8KP33)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>



