



USB 3.1 Type C to Dual Display Converter

Part No.: 43179

Description

- Converts a USB 3.1 Type C port to an HDMI and VGA port
- Requires DisplayPort Alternate Support by the USB 3.1 Port/Bus
- Supports resolutions up to 3840x2160@30Hz 8bit RGB (HDMI) / 1920x1080@60Hz (VGA)
- Plug and Play, no drivers required
- 2 year warranty

The Lindy USB 3.1 Type C to Dual Display Converter allows users to connect two high definition screens to a Macbook, ultrabook or notebook with USB 3.1 DisplayPort Alternate Mode. With support for both SST (Single Stream Transport) and MST (Multi-Stream Transport) the Converter can send the same display information to two screens (SST) or use both screens as individual displays with separate display information (MST), this is easily configured using the display settings of your computer.

Installation is simple as no drivers are required, while Type-C's reversible design has been developed to work regardless of which way the cable is inserted into the port.

Technical details

Specifications

- AV Interface: USB Type C to HDMI & VGA
- Interface Standard: HDMI, VGA
- Supported Bandwidth: -
- Maximum Input Resolution: 3840x2160@30Hz 8bit RGB (HDMI) / 1920x1080@60Hz (VGA)
- Maximum Output Resolution: 3840x2160@30Hz 8bit RGB (HDMI) / 1920x1080@60Hz (VGA)
- Chipset: Synaptics VMM3332BJGR
- Compatibility: USB Type C or Thunderbolt 3 equipped computers with DisplayPort Alternate

Mode support

- Power Delivery: -
- HDCP Support: HDCP 1.4
- Supported Audio: -
- Separate Audio Ports: -
- Special Features: DisplayPort Alternate Mode, SST & MST support

Connectors

- Inputs: 1 x USB Type C (Male)
- Outputs: 1 x HDMI (Female), 1 x VGA (Female)
- Power: Bus-powered

Physical Properties

- Dimensions (approx.) WxDxH: 55x45x15mm (2.17x1.77x0.59in)
- (Fixed) Cable Length: 140mm (5.51in)
- Housing Material: Plastic
- Net Weight: 0.02kg (0.04lb)
- Operating Temperature: 0°C - 50°C (32°F - 122°F)
- Storage Temperature: -20°C - 70°C (-4°F - 158°F)
- Humidity: 0 - 90% RH (non-condensing)
- Power Requirements: -
- Colour: White

Miscellaneous

- Packaging Type: Carton Box
- Packaging Dimensions: 165x80x25mm (6.5x3.15x0.98in)
- Gross Weight: 0.05kg (0.11lb)
- Warranty (Years): 2
- Certificated: CE, FCC, RoHS & REACH

Package content

- USB 3.1 Type C to Dual Display Converter
- Lindy Manual

Purchasing information

- No.: 43179
- EAN: 4002888431798