

CD-HF 75X75 5/7.5 DKG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Similar to illustration

Increase your wiring flexibility with our comprehensive range of accessories available from a single source. The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sized holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

General ordering data

| | |
|------------|--|
| Type | CD-HF 75X75 5/7.5 DKG |
| Order No. | 2589340000 |
| Version | Halogen-free cable duct, 75 mm x 75 mm, 5.00 mm x 7.50 mm, 2000 mm |
| GTIN (EAN) | 4050118603637 |
| Qty. | 16 m |

CD-HF 75X75 5/7.5 DKG

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|----------|-----------------|------------|
| Length | 2,000 mm | Length (inches) | 78.74 inch |
| Width | 75 mm | Width (inches) | 2.953 inch |
| Height | 75 mm | Height (inches) | 2.953 inch |
| Net weight | 675 g | | |

General information

| | | | |
|----------------------|---|---------------------------|---------|
| Colour | dark grey | Cover | Yes |
| Flexible wiring duct | No | Halogen | No |
| Material | PPE | Non-tracking | Yes |
| Slit gap | 7.5 mm | Slit width | 5 mm |
| Type of mounting | when screwed in, With adhesive, Riveted | UL 94 flammability rating | V-0 |
| Usable cross-section | 4,930 mm ² | Version of side panel | slotted |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 6.0 | EC000012 | eClass 6.2 | 27-40-07-03 |
| eClass 9.1 | 27-40-07-03 | | |

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data [STEP](#)

CD-HF 75X75 5/7.5 DKG

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

