

C6T (RF EDITION)

SEAMLESSLY CONNECT TO YOUR HOME, YOUR OFFICE, YOUR STORE. AND COMMUNICATE WITH YOUR FAMILY AND PETS. INTEGRATED HUB MODULE, EASILY CONNECT TO EZVIZ SENSORS TO GUARD YOUR HOME



With the C6T (RF Edition) you always enjoy peace of mind. The ez360 lets you control your home, your store, or your office from almost any angle. Is the baby sound asleep? Is the dog doing okay? Is your store or office secure? Just check the app on your smartphone, wherever you are, whenever you want.



HIGHLIGHTS



Alarm system

Integrated Hub module, connect to your sensors directly



Full HD resolution

Crystal clear images and videos



Pan/Tilt function

Easily to get panoramic views



Night vision up to 10 metres

See what's happening, even in the dark



Smart Privacy Mask

Privacy when needed



Easy-to-use app

Crisp layout, user-friendly features



Smart tracking

Track moving objects and record videos



WiFi-ready

No cables required. Plug and go



Built-in 2-way audio

Microphone and speaker inside



Local storage

Store on an SD card or a NVR



32 sensors Max. Access

Fully guard your office, home, etc.

ABOUT EZVIZ

EZVIZ helps you to app your life. Right from the palm of your hand, you connect visually to your home or your work. Welcome to the smart home and business!

FEATURES



ALARM SYSTEM

Integrated Hub module, connect to all EZVIZ sensors (PIR, sirens, water leaks, doors and windows) directly. Link the sensors with the camera, the Camera will start recording and tracking when the sensor is triggered. All-round security at your fingertips.




ALWAYS CONNECTED. ALWAYS SAFE

HD live streaming. Don't miss a moment of what's happening. Check the app whenever you want.



360° PANORAMIC VIEW

The smart helmet has a Pan/Tilt function. You can see every angle of the room, using your phone as a remote control.



SMART MOTION TRACKING

The C6T (RF Edition) tracks all moving objects using its smart motion sensor. You can record videos on an SD card or NVR (network video recorder).



PRIVACY WHEN NEEDED

When you activate the privacy mode, the lens moves back into its helmet and immediately stops recording audio and video and disables live viewing.



SEE WHAT'S HAPPENING, EVEN IN THE DARK

The camera automatically switches to night vision when it's dark. You can watch over your baby's sleep without making any noise or check your store or office during the night.

FEATURES



32 SENSORS MAX. ACCESS

2 sensors inside the box. If you find out it is not enough, you can buy other EZVIZ sensors separately and connect to the camera.

ALWAYS UP-TO-DATE

Whenever movement is detected, an instant alert is sent to your mobile phone via an app notification. Know what's happening when it's happening.

LISTEN IN AND TALK

The C6T (RF Edition) comes with a built-in speaker and microphone. Just open the app and listen in or talk to the room using the speaker when there's an intruder or the dog's sleeping on the sofa.

STORE AND SHARE IMPORTANT MOMENTS

The camera has an integrated micro SD card slot that supports up to 128 GB of storage. Ideal to keep a funny videos of your toddler. You can also store the pictures and videos on the EZVIZ wireless NVR (network video recorder).

INTEGRATED EZVIZ SOLUTION

The C6T (RF Edition) connects with all EZVIZ sensors (for pets, sirens, water leaks, doors and windows). All-round security at your fingertips.

ONE APP DOES ALL THE WORK

With the easy-to-use EZVIZ app, you can view up to four live video streams at the same time. You can connect all your EZVIZ security devices on one and the same app.



SPECIFICATIONS



CAMERA

Image sensor	2 megapixel 1/3" Progressive Scan CMOS
Shutter	Self-adaptive shutter
Lens	4mm@ F2.2, Diagonal angle : 95°
PT Angle	Pan: 340° Tilt: 90°
Lens Mount	M12
Day & Night	IR cut filter
DNR	3D DNR
WDR	Digital WDR

COMPRESSION

Video Compression	H.264
H.264 Type	Main Profile
Video Bit Rate	HD; balance; and fluency. Adaptive bit rate
Audio Compression	AAC
Audio Bit Rate	Adaptive bit rate

IMAGE

Max. Resolution	1920x1080
Frame Rate	Network transmission frame rate: adaptive adjustment
BLC	Support

NETWORK

Storage	Support Micro SD card (Max. 128G)
Smart Alarm	Motion detection
One-key configuration	SmartConfig (Wi-Fi one-key configuration)
Protocols	Ezviz cloud proprietary protocol
Interface Protocol	Ezviz cloud proprietary protocol
General Function	Flicker filter, dual-stream, heartbeat, mirror image, password protection, watermark

WIRELESS PARAMETERS

Standard	IEEE802.11b, 802.11g, 802.11n
Frequency Range	2.4 GHz ~ 2.4835 GHz
Channel Bandwidth	Support 20/40MHz
Security	64/128-bit WEP, WPA/WPA2, WPA-PSK/WPA2-PSK, WPS
Transmission Rate	11b: 11Mbps, 11g :54Mbps, 11n :135Mbps

GENERAL

RF Module	Carrier frequency 868MHz, support up to 32 various sensor
Operating Conditions	-10° ~ 55°, Humidity 95% or less (non-condensing)
Power Supply	DC 5V±10%
Power Consumption	8W MAX
IR Range	MAX 10 meters
Dimensions (mm)	100mm x 100mm x 90mm
Weight	220g

What's in the box?

- 1 x C6T (RF Edition)
- 1 x Remote Controller
- 1 x Wireless magnetic contact
- 1 x Base
- 1 x Power Cable
- 1 x Power Adapter
- 1 x Drill Template
- 1 x Screw Kit
- 1 x Quick Start Guide