THM
THM WO 33.5/93.1 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Similar to illustration

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Type	THM WO 33.5/93.1 GE
Order No.	1774410000
Version	THM, Conductor and cable markers, 8 - 21.7 mm, 33.5 x 93.1 mm, yellow
GTIN (EAN)	4032248148592
Qty.	1 pc(s).
compatible printer	2430920000 2448870000

THM
THM WO 33.5/93.1 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	93.1 mm	Width (inches)	3.665 inch
Height	33.5 mm	Height (inches)	1.319 inch
Depth	0.025 mm	Depth (inches)	0.001 inch
Net weight	284 g		

General data

Adhesive	Polyacrylate adhesive	Colour	yellow
Halogen	No	Material	Polyester film
Material colour according to resistance code	4	Number per roll	500
Operating temperature range	-40…150 °C	Size of labelling field	33.5 x 25 mm
Type of printing	neutral	UL 94 flammability rating	V-0
Version	Self-adhesive	Width	93.1 mm

Conductor and cable markers

Conductor O.D.	8 - 21.7 mm	Conductor O.D., max.	21.7 mm
Conductor O.D., min.	8 mm	Conductor cross-section, max.	400 mm²
Conductor cross-section, min.	0.75 mm²	Halogen	No

Classifications

ETIM 3.0	EC001530	ETIM 4.0	EC001288
ETIM 5.0	EC001530	ETIM 6.0	EC001530
UNSPSC	44-12-17-08	eClass 5.1	27-14-91-03
eClass 6.2	27-40-04-01	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-03	eClass 9.0	27-40-04-01
eClass 9.1	27-40-04-01		

Approvals

ROHS	Conform

Downloads

Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
Software	M-Print PRO configuration file

THM
THM WO 33.5/93.1 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

