

# F204 A-40/0,03 AP-R



F204 A-40/0,03 AP-R Residual Current Circuit Breaker

## General Information

Extended Product Type	F204 A-40/0,03 AP-R
Product ID	2CSF204401R1400
EAN	8012542785507
Catalog Description	F204 A-40/0,03 AP-R Residual Current Circuit Breaker
Long Description	The RCCBs F200 series assures protection to people and installations against fault current to earth. A large offer for standard instantaneous and selective AC and A types is completed with some configurations for special applications. This product provides the best compromise between safety and continuity in the service, thanks to the resistance to unwanted trippings.

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363030

## Popular Downloads

Data Sheet, Technical Information	9AKK107046A0424
Instructions and Manuals	Manual sheet inside the box

## Dimensions

Product Net Width	0.070 m
Product Net Height	0.085 m
Product Net Depth / Length	0.069 m
Product Net Weight	0.360 kg

## Technical

Standards	IEC/EN 61008 UL 1053
Operating Characteristic	Instantaneous (APR High Immunity)
Type of Residual Current	A type
Rated Residual Current	30 mA
Rated Current ( $I_n$ )	40 A
Number of Poles	4
Position of Neutral Terminals	Right

Power Loss	at Rated Operating Conditions per Pole 3.2 W
Rated Voltage (U <sub>r</sub> )	230/400 V

---

## Environmental

Ambient Air Temperature	Operation -25 ... +55 °C Storage -40 ... +70 °C
RoHS Status	Following EU Directive 2011/65/EU

---

## Technical UL/CSA

Maximum Operating Voltage UL/CSA	480Y / 277 V AC
----------------------------------	-----------------

---

## Certificates and Declarations (Document Number)

Declaration of Conformity - CE	9AKK106713A5602
Environmental Information	Refer to RoHS
Instructions and Manuals	Manual sheet inside the box
RoHS Information	2CSC423001K2702

---

## Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	0.082 m
Package Level 1 Height	0.078 m
Package Level 1 Depth / Length	0.096 m
Package Level 1 Gross Weight	0.403 kg
Package Level 1 EAN	8012542785507

---

## Classifications

Object Classification Code	Q
E-nummer	2160178
ETIM 4	EC000003 - Residual current circuit breaker (RCCB)
ETIM 5	EC000003 - Residual current circuit breaker (RCCB)
ETIM 6	EC000003 - Residual current circuit breaker (RCCB)
ETIM 7	EC000003 - Residual current circuit breaker (RCCB)

---

## Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Residual Current Devices RCDs → Residual Current Devices RCDs

