

# Data Sheet

## 320pcs Crimp blade connectors assortment with insulators



Household appliances use crimp blade connectors from 2.8mm to 6.3mm, which are widely available. This practical range consists of the most common blade connectors, soft insulating sleeves and hard plastic protecting boots - ideal for repair and maintenance. The compilation includes the cross sections from 0.5 mm<sup>2</sup> to 2.5 mm<sup>2</sup> for fine and superfine conductors. Connection angle 180°. Material: electrolytic copper.



**Contents:**


- 2.8 x 0.8 blade connector , cross section 0.5~1.0mm<sup>2</sup> - 30pcs
- 2.8 x 0.8 blade connectore, cross section 1.5~2.5mm<sup>2</sup> - 30pcs
- 4.8 x 0.8 blade connector, cross section 0.5~1.0mm<sup>2</sup> - 25pcs
- 4.8 x 0.8 blade connector, cross section 1.5~2.5mm<sup>2</sup> - 25pcs
- 6.3 x 0.8 blade connector, cross section 0.5~1.5mm<sup>2</sup> - 18pcs
- 6.3 x 0.8 blade connector, cross section 1.5~2.5mm<sup>2</sup> - 18pcs
- PVC cover for 2.8 mm connector,Red,Blue,Transparent @ 25pcs
- PVC cover for 4.8mm connector, Red,Blue,Transparent @ 18pcs
- PVC cover for 6.3mm connector, Red,Blue,Transparent @ 15pcs

**Blade connector**



Tab (mm)	Cross section (mm <sup>2</sup> )	L (mm)	h (mm)	W1 (mm)	W2 (mm)
2.8 x 0.8	0.5 - 1.0	16.0	4.7	2.8	2.9
	1.5 - 2.5	16.0	4.3	2.8	3.8
4.8 x 0.8	0.5 - 1.0	17.0	4.4	4.8	3.0
	1.5 - 2.5	17.0	4.7	4.8	3.5
6.3 x 0.8	0.5 - 1.0	20.0	4.3	6.3	3.2
	1.5 - 2.5	20.0	4.5	6.3	3.8

**PVC insulating sleeve**



Suitable for tab(mm)	L (mm)	L1 (mm)	d1 (mm)	d2 (mm)	w (mm)
2.8 x 0.8	23.0 ± 2.0	15.5 ± 1.5	4.0	∅3.0	1.8
4.8 x 0.8	23.0 ± 2.0	15.5 ± 1.5	5.0	∅3.0	2.3
6.3 x 0.8	25.0 ± 2.0	18.0 ± 2.0	8.0	∅3.5	3.5

