

DECT business telephone

Aastra 610d

The Aastra 610d of the Aastra 600d DECT telephone family is the basic model for the business sector.

With its illuminated monochrome 2" display it guarantees an optimum overview and simple operation of the clearly structured menus at all times. It also supports service facilities like firmware download over air¹ which helps to reduce support costs.

The ambient noise filter can automatically adjust the ring tone and talk volume to the background noise in any given situation and filters out any distracting ambient noise. Ensuring optimum communication conditions at all times, especially in loud environments.

Important events – reminders, incoming call signals, warning of exceeding the system range or indication of battery charge status are all indicated by a 3-colour LED on the handset.



Aastra 610d

Highlights of the Aastra 610d

- ✦ LC-display (2", 176 x 160 dots, monochrome)
- ✦ Telephone book for 200 contacts¹, with 7 possible entries each: office, private, mobile and fax number¹, email address¹; ringing tone and quick dialling assignment¹
- ✦ Ambient noise filter for loud environments
- ✦ 44 polyphone (Midi type) and 8 normal
- ✦ Ring tones with automatic volume control can be assigned
- ✦ Up to 5 user profiles for e.g. headset or meeting usage can be configured
- ✦ Hands free operation
- ✦ Headset connector (2.5 mm jack)
- ✦ 2 programmable navigation keys¹
- ✦ 3 colour multi-purpose LEDs which can be set for signalling numerous operation modes
- ✦ User-friendly, wireless function and firmware updates via the cellular network (download over air)¹.
- ✦ The intelligent battery management guarantees an overview of the battery capacity at all times, even in cases where an empty battery has been replaced with one that is supposedly fully charged.

¹ if supported by PABX

Local Features

- * Key lock (shortcut: # key)
- * 3 soft keys for menu control (two of which are programmable¹)
- * Ring tone volume adjustable
- * Ring tone off (shortcut: Asterisk key)
- * Different ring tones for: internal-, external calls, messages, alarm call, emergency call¹
- * Signal tones for key click, confirmation, battery empty, out of range
- * Different earpiece-, speaker- and headset volume
- * Display with 6 text lines, 1 headline and 1 soft key line
- * Handset name can be edited
- * Display contrast adjustable
- * Illumination time for display and keypad can be adjusted separately (separate values while in / out of charger)
- * Dim function for display light
- * Alarm and appointment settings for 3 different times each¹
- * Automatic quick dialling by pressing numeric key¹
- * Automatic / Manual key lock
- * Telephone lock with 4-digit PIN
- * Automatic answer when removed from the charger
- * Silent charging
- * Caller list with 30 entries¹

- * Redial list with 20 entries¹
- * Display languages: Czech, Danish, Dutch, German, English, Finnish, French, Italian, Norwegian, Polish, Portuguese, Russian, Slovene, Spanish, Swedish¹
- * +, - volume keys
- * Time and date (manually or by PABX¹)

Administration Features

- * Automatic firmware update "over air"¹
- * Integrated diagnostic functions

Technical Data

- * Standards: DECT, GAP
- * Ingress protection: IP 50
- * Supports DECT-encryption
- * Stand-by-time: at least 100 h EMEA / 95 h US
- * Talk time: at least 12 h EMEA / 15 h US
- * Standard battery: Lithium-Ion battery pack
- * Free fall: 1.5 m on concrete without damage
- * Dimensions (W x H x D):
49 x 135 x 22.5 mm
- * Weight with Standard battery: 120 g
- * International AC Adapter for EMEA, North America and Australia

Part numbers

- * Handset with belt clip "Easy", standard battery, cradle with international AC-adapter and quick user guide
68851
- * Cradle with international AC-adapter
68980
- * Handset Aastra 610d with standard battery
68983
- * Belt clip "Rotary"
68770
- * Lanyard attachment
68769
- * Leather poach
68762
- * Charger Rack including 8 rack charger
68774



Aastra 610d in leather poach



Charger Rack including 8 rack charger

¹ if supported by PABX

Aastra Technologies Limited
155 Snow Blvd.
Concord, Ontario Canada
L4K 4N9
www.aastra.com

Reference 04/2011



Copyright © 2011 Aastra Technologies Limited. Aastra and the Aastra logo are trademarks or registered trademarks of Aastra Technologies Limited in the United States, Canada, European Union and other countries. Picture similar to product. The right for technical modifications is reserved.

AASTRA