

**cable lug, terminal end
KQN-M4/S/-2,5**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KQN-M4/S/-2,5
Order No.	1493840000
Version	cable lug, terminal end, 1,5 mm ² - 2,5 mm ²
GTIN (EAN)	4050118303391
Qty.	100 pc(s).

cable lug, terminal end KQN-M4/S/-2,5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Weight	0.06 g	Net weight	0.639 g
--------	--------	------------	---------

Connectors

Conductor cross-section, max.	2.5 mm ²	Conductor cross-section, min.	1.5 mm ²
Connection length (l)	11 mm	Hole	M 4/S
Inside diameter of flange (d2)	4.3 mm	Inside diameter of shaft (d1)	2.3 mm
Insulation	not available	Outside diameter of shaft (d3)	6.8 mm
Shaft length (a)	5 mm		

Classifications

ETIM 3.0	EC001509	ETIM 4.0	EC001509
ETIM 5.0	EC001052	ETIM 6.0	EC001059
eClass 6.2	27-40-02-04	eClass 7.1	27-40-02-04
eClass 8.1	27-40-02-04	eClass 9.0	27-40-02-12
eClass 9.1	27-40-02-12		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN

Data sheet**cablE lug, terminal end
KQN-M4/S/-2,5**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings