

## Tools

### Powerstripper AM 12

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- for automatic stripping of individual wires
- stripping of flexible wires according to DIN VDE 0295, Cl. 5
- Partial stripping of insulation, the isolation remains on wire end
- Change of tools not necessary
- Quick and easy setting for the proper cross-section
- Stripping length from 3 to 20 mm
- Min. conductor length: 22 mm + stripping length
- Electric drive

#### General ordering data

Type	Powerstripper AM 12
Order No.	<a href="#">1534740000</a>
Version	Automatic machines, Automatic stripper
GTIN (EAN)	4050118338409
Qty.	1 pc(s).

## Tools Powerstripper AM 12

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	254 mm	Width (inches)	10 inch
Height	520 mm	Height (inches)	20.472 inch
Depth	230 mm	Depth (inches)	9.055 inch
Weight	17 kg	Net weight	17,000 g

### Technical data

Electrical connection	100-240 V / 50/65 Hz
-----------------------	----------------------

### Automatic stripping

Compressed-air connection	5.5 bar	Drive	Electropneumatic
Electrical connection	100-240 V / 50/65 Hz	Insertion length	80 mm
Max. dismantling area	11.9	Max. dismantling length	120
Min. dismantling area	3.5 mm	Min. dismantling length	25
Pull-off length	20 - 120 mm	Pulse time	approx. 3 s

### Classifications

ETIM 3.0	EC000163	ETIM 6.0	EC002778
eClass 6.2	17-13-01-02	eClass 7.1	17-13-01-02
eClass 8.1	17-13-01-02	eClass 9.0	17-13-01-01
eClass 9.1	17-13-01-02		

### Approvals

ROHS	Conform
------	---------

### Downloads

Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a>
User Documentation	<a href="#">Powerstripper AM 12</a> <a href="#">Powerstripper AM 12</a>

**Tools**  
**Powerstripper AM 12**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

