

**SwitchMark**  
**SM 27/18-22 MM WS VPE100**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Prevention of incorrect operation: SM**

MultiMark device markers can be used with marking materials from different manufacturers. Wherever they are used, they ensure that all components, such as control and signalling devices from different vendors, are clearly assigned.

**Your benefits with MultiMark**

- Double laminated polyester
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

**General ordering data**

|                    |                                                       |
|--------------------|-------------------------------------------------------|
| Type               | SM 27/18-22 MM WS VPE100                              |
| Order No.          | <a href="#">2496960000</a>                            |
| Version            | SwitchMark, Device markers, 47.75 x 27 mm, white      |
| GTIN (EAN)         | 4050118508468                                         |
| Qty.               | 100 pc(s).                                            |
| compatible printer | <a href="#">2430920000</a> <a href="#">2448870000</a> |

## SwitchMark SM 27/18-22 MM WS VPE100

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technical data

### Dimensions and weights

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Width      | 27 mm    | Width (inches)  | 1.063 inch |
| Height     | 47.75 mm | Height (inches) | 1.88 inch  |
| Depth      | 0.1 mm   | Depth (inches)  | 0.004 inch |
| Net weight | 0.1 g    | Diameter        | 22 mm      |

### General data

|                         |                             |                             |              |
|-------------------------|-----------------------------|-----------------------------|--------------|
| Adhesive                | Acrylate adhesive           | Approval acc. to UL 969     | Yes          |
| Colour                  | white                       | Halogen                     | No           |
| Material                | Polyester                   | Operating temperature range | -40...120 °C |
| Size of labelling field | 18 x 27 mm                  | UL 94 flammability rating   | V-0          |
| Version                 | halogen-free, Self-adhesive | Width                       | 27 mm        |

### Device markers

|          |       |
|----------|-------|
| Diameter | 22 mm |
|----------|-------|

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 6.0   | EC001288    | eClass 6.2 | 27-14-91-29 |
| eClass 9.0 | 27-40-06-29 | eClass 9.1 | 27-40-06-29 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                  |                       |
|------------------|-----------------------|
| Engineering Data | <a href="#">EPLAN</a> |
|------------------|-----------------------|

### SwitchMark SM 27/18-22 MM WS VPE100

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

