



## Thunderbolt 3 to Dual HDMI Converter

Part No.: 43900

### Description

- Connects two HDMI displays through a single Thunderbolt 3 port
- Supports HDMI resolutions up to Ultra HD 4K 3840x2160@60Hz on two monitors
- Peak performance with Thunderbolt 3's 40Gbps bandwidth
- Compatible with Thunderbolt 3 equipped Windows and Mac computers
- 2 year warranty

The Lindy Thunderbolt 3 to Dual HDMI Converter allows to run resource intensive applications on two 4K 60Hz HDMI displays through a single Thunderbolt 3 port of your PC or Mac. Only Thunderbolt 3 with its incredible bandwidth of 40Gbps allows one 5K or two 4K 60Hz displays simultaneously while outputting video and audio signal at the same time. It is an essential tool for professional creatives to streamline their workflows, no matter whether for photo and video editing, rendering in real-time, 3D graphics, virtual reality or computer-aided design. Thunderbolt 3 helps to avoid bottlenecks for demanding work in general.

Designed for notebook or ultrabook users, the converter creates the ability to have two independent monitors connected as well as the flexibility to configure the layout of the displays into Extended or Mirrored Desktop modes\* making it suitable for almost any application. Please note that Thunderbolt 3 uses the USB Type C connector, but only Thunderbolt 3 equipped computers - not USB 3.1 or USB 3.0 Type C equipped computers - support this converter.

\* mac OS only supports mirrored mode, no extended mod

### Technical details

#### Specifications

- AV Interface: Thunderbolt 3 to HDMI

- Interface Standard: Thunderbolt 3, HDMI 2.0
- Supported Bandwidth: 40Gbps
- Maximum Input Resolution: 3840x2160@60Hz
- Maximum Output Resolution: 3840x2160@60Hz
- Chipset: Intel Alpine Ridge 4C, Parade PS176 (HDMI), TI TPS65983A (PD)
- Compatibility: Thunderbolt 3 equipped computers
- Power Delivery: -
- HDCP Support: HDCP 2.2
- Supported Audio: -
- Seperate Audio Ports: -
- Special Features: -

## Connectors

- Inputs: 1 x USB Type C (Male)
- Outputs: 2 x HDMI (Female)
- Power: Bus-powered

## Physical Properties

- Dimensions (approx.) WxDxH: 100x60x15mm (3.94x2.36x0.59in)
- (Fixed) Cable Length: 270mm (10.63in)
- Housing Material: Aluminium, plastic side parts
- Net Weight: 0.09kg (0.2lb)
- Operating Temperature: 0°C - 40°C (32°F - 104°F)
- Storage Temperature: -20°C - 70°C (-4°F - 158°F)
- Humidity: 20 - 90% (non-condensing)
- Power Requirements: -
- Colour: Silver, black

## Miscellaneous

- Packaging Type: Carton box
- Packaging Dimensions: 151x83x26mm (5.94x3.27x1.02in)
- Gross Weight: 0.14kg (0.31lb)
- Warranty (Years): 1
- Certificated: CE, FCC, RoHS & REACH

## Package content

- Thunderbolt 3 to Dual HDMI Converter
- Lindy Manual

## Purchasing information

- No.: 43900
- EAN: 4002888439008

