



USB 3.1 Type C to HDMI 4K60 Converter with Power Delivery

Part No.: 43178

Description

- Adds an HDMI port and a USB Type C power supply port to your computer
- Supports HDMI resolutions up to 4K 4096x2160@60Hz 8Bit RGB
- Requires DisplayPort Alternate Mode support by the USB 3.1 Port/Bus
- Supports Type C power supplies up to 60W
- 2 year warranty

The Lindy USB 3.1 Type C to HDMI 4K60 Converter allows users to easily add external video capabilities to a computer featuring the USB 3.1 Type C port with support for DisplayPort Alternate Mode. USB Power Delivery of up to 60W provides power to a notebook or ultrabook via its USB Type C port whilst simultaneously using it as a video output, simply connect a compatible USB power supply to the HDMI Converter.

With support for 4K UltraHD resolutions, content can be viewed with superior clarity and stunning accuracy, while Type-C's reversible design has been developed to work regardless of which way the cable is inserted into the port of a laptop, notebook or Macbook.

With Plug and Play installation, this converter can be installed with minimum fuss, perfect for both professional and first time users.

Technical details

Specifications

- AV Interface: USB Type C to HDMI
- Interface Standard: HDMI 2.0
- Supported Bandwidth: -
- Maximum Input Resolution: 4096x2160@60Hz 8bit RGB

- Maximum Output Resolution: 4096x2160@60Hz 8bit RGB
- Chipset: PS176, VL100, RTD2168
- Compatibility: USB Type C or Thunderbolt 3 equipped computers with DisplayPort Alternate Mode support
- Power Delivery: PD 2.0 up to 60W (20V 3A)
- HDCP Support: HDCP 1.4
- Supported Audio: -
- Separate Audio Ports: -
- Special Features: DisplayPort Alternate Mode

Connectors

- Inputs: 1 x USB Type C (Male)
- Outputs: 1 x HDMI (Female)
- Power: -

Physical Properties

- Dimensions (approx.) WxDxH: 33x50x12mm (1.3x1.97x0.47in)
- (Fixed) Cable Length: 150mm (5.91in)
- Housing Material: Plastic
- Net Weight: 0.02kg (0.04lb)
- Operating Temperature: 0°C - 50°C (32°F - 122°F)
- Storage Temperature: -20°C - 70°C (-4°F - 158°F)
- Humidity: 0 - 90% RH (non-condensing)
- Power Requirements: -
- Colour: White

Miscellaneous

- Packaging Type: Carton Box
- Packaging Dimensions: 165x80x25mm (6.5x3.15x0.98in)
- Gross Weight: 0.06kg (0.13lb)
- Warranty (Years): 2
- Certificated: CE, FCC, RoHS & REACH

Package content

- USB 3.1 Type C to HDMI Converter
- Lindy Manual

Purchasing information

- No.: 43178
- EAN: 4002888431781

