



USB 3.1 Type C to HDMI Converter with Power Delivery

Part No.: 43196

Description

- Adds an HDMI port and a USB Type C power supply port to your computer
- Supports HDMI resolutions up to 4K 3840x2160@30Hz
- Requires DisplayPort Alternate Mode support by the USB 3.1 Port/Bus
- Supports Type C power supplies up to 60W
- 2 year warranty

The Lindy USB 3.1 Type C to HDMI Converter allows users to easily add external video capabilities to your computer featuring the USB 3.1 Type C port with support for DisplayPort Alternate Mode. USB Power Delivery of up to 60W provides power to a notebook or ultrabook via its USB Type C port whilst simultaneously using it as a video output, simply connect a compatible USB power supply to the HDMI Converter.

With support for 4K UltraHD resolutions, content can be viewed with superior clarity and stunning accuracy, while Type-C's reversible design has been developed to work regardless of which way the cable is inserted into the port of a laptop, notebook or Macbook.

With Plug and Play installation, this converter can be installed with minimum fuss, perfect for both professional and first time users.

Technical details

Specifications

- AV Interface: USB Type C to HDMI
- Interface Standard: HDMI 1.4b
- Supported Bandwidth: 8.9Gbps
- Maximum Input Resolution: 3840x2160@30Hz 4:4:4

- Maximum Output Resolution: 3840x2160@30Hz 4:4:4
- Chipset: NXP (PS171, QFN-56), LN6206P332M, SOT23
- Compatibility: USB Type C or Thunderbolt 3 equipped computers with DisplayPort Alternate Mode support
- Power Delivery: PD 2.0 up to 60W (20V 3A)
- HDCP Support: HDCP 1.4
- Supported Audio: 8 Channel LPCM, Dolby True HD, DTS-HD MA
- Separate Audio Ports: -
- Special Features: DisplayPort Alternate Mode

Connectors

- Inputs: 1 x USB Type C (Male)
- Outputs: 1 x HDMI (Female)
- Power: -

Physical Properties

- Dimensions (approx.) WxDxH: 43x40x15mm (1.69x1.57x0.59in)
- (Fixed) Cable Length: 170mm (6.69in)
- Housing Material: Plastic
- Net Weight: 0.029kg (0.06lb)
- Operating Temperature: 0°C - 50°C (32°F - 122°F)
- Storage Temperature: -10°C - 70°C (14°F - 158°F)
- Humidity: 0 - 90% RH (non-condensing)
- Power Requirements: -
- Colour: White

Miscellaneous

- Packaging Type: Polybag
- Packaging Dimensions: 160x160x20mm (6.3x6.3x0.79in)
- Gross Weight: 0.03kg (0.08lb)
- Warranty (Years): 2
- Certificated: CE, FCC, RoHS & REACH

Package content

- USB 3.1 Type C to HDMI Converter
- Lindy Manual

Purchasing information

- No.: 43196
- EAN: 4002888431965

