

Accessories

Jackscrew with Slot

TECHNICAL SPECIFICATIONS

Jackscrew with Slot

Suits all standard hoods equipped with a "hook" for securing the screw position inside the hood.

Example:
DPPK / DSSK / DTZK / D45ZK - Series etc.



Order Code:	Name:
6826-0134-01	Jackscrew with Slot

Accessories

Long Full Metal Thumbscrews

TECHNICAL SPECIFICATIONS

Long Full Metal Thumbscrews:

Suits all standard hoods equipped with a "hook" for securing the screw position inside the hood.

Example:
DPPK / DSSK / DTZK / D45ZK - Series etc.



Order Code:	Name:	Thread / Length:
6826-0141-02	Blank JS	UNC 4-40 / 47mm
6826-0141-01	Blank JS	UNC 4-40 / 31,5mm
6826-0142-02	Black Chr. JS	UNC 4-40 / 47mm
6826-0142-03	Black Chr. JS	UNC 4-40 / 31,5mm

Accessories

Short Full Metal Jackscrews

TECHNICAL SPECIFICATIONS

Short Full Metal Jackscrews:

Suits following Series:

DSSK-Series Plastic & Metalized
TRI - Series Plastic & Metalized (18.1mm only)
DTNT-Series Plastic & Metalized (12.1mm only)



Order Code:	Name:	Thread / Length:
6826-0133-01	JS-DSSK	UNC 4-40 / 18,1mm
6826-0133-04	JS-DSSK	UNC 4-40 / 12,1mm
6826-0133-11	JS-DSSK-BK	UNC 4-40 / 18,1mm
6826-0133-14	JS-DSSK-BK	UNC 4-40 / 12,1mm

Accessories

Full Metal Jackscrews

TECHNICAL SPECIFICATIONS

Full Metal Jackscrews:

Suits following Series:
DTZF and D45ZF - Series



Order Code:	Name:	Thread / Length:
2099-0002-01	FRS1/5	UNC 4-40 / 43.5mm
2099-0002-02	FRS1/5-K333	UNC 4-40 / 27.3mm
2099-0002-03	FRS1/5-K364	UNC 4-40 / 22.5mm
2099-0002-11	FRS1/5-M3	M3 / 43.5mm
2099-0002-12	FRS1/5-K333-M3	M3 / 27.3mm
2099-0002-13	FRS1/5-K364-M3	M3 / 22.5mm
2099-0002-21	FRS1/5-M2.5	M2.5 / 43.5mm
2099-0002-22	FRS1/5-K333-M2.5	M2.5 / 27.3mm
2099-0002-23	FRS1/5-K364-M2.5	M2.5 / 22.5mm
2099-0003-01	FVS1/5-K1163	UNC 4-40 / 18mm
2099-0003-11	FVS1/5-K1163-M3	M3 / 18mm
2099-0003-21	FVS1/5-K1163-M2.5	M2.5 / 18mm

