

SIRIO

Modern design and technology for a quick and programmed heating



Wheels for Portable use (optional)


The brand new range of convection heaters SIRIO by Radialight provides the most simple and economical yet advanced solution to domestic heating, while decorating your home with their modern design.

The inner aluminium heating core provides all the heat necessary to reach the required temperature as quickly as possible and, in combination with the integrated electronic thermostat, SIRIO is able to maintain the comfort level you want, with absolute, long-lasting precision.

Weekly programming, open window detection and led display: everything is designed to get a quick temperature rise and the maximum energy savings for your immediate well-being.


SIRIO convectors are light-weight and easy to install, thanks to the complete kit that comes with each product. In less than 15 minutes you can benefit from the warm embrace offered by SIRIO, without any building works and invasive electrical connections.

Heating Style



SIRIO will heat your home using natural convection - the cold air passes through the lower grille, is heated by the aluminium coil, and comes out of the grille at the top, heating your domestic environments perfectly, in complete safety and without any noise, as there are no moving mechanical parts. The electronic thermostat provides intelligent heat management, automatically reducing consumption when the temperature reaches the required level.

Control System



Intuitive user experience with the new SIRIO interface


1 Lcd Display - 2 Mode settings - 3 Function settings - 4 Up/Down arrows - 5 Stand-by

SIRIO is fitted with an adjustable digital thermostat enabling the room temperature to be controlled, with an accuracy of 0,2°C. Choose among 5 heating modes: Comfort, Comfort -1°C, Comfort -2°C, Eco - 3,5°C and Frost protection.

Weekly programmable room temperature and heating period + the open window detection function allows you to adapt the working time of SIRIO to your everyday life and also to save energy.

Features

- Electric Convector slim and stylish design - only 10,2 cm thick, that ensure quick, uniform heating of the space
- Backlight LCD Display screen
- Maximum silence - no moving mechanical parts (fan or motors) included
- Energy-saving technology with consumption optimisation
- Weekly programming, Open window detection and Lock function
- Easy, quick installation using the built-in assembly kit, and zero maintenance costs
- Wheels are supplied as optional to make the convector portable for carrying
- IP24 protection against sprayed water, ideal for installation in wet spaces as well
- Lot 20 ERP ECO DESIGN Compliant



Technical data

The SIRIO range is available in 4 different models – from 500W, 1000W, 1500W, to 2000W – whose size and power are designed to meet the needs of every home environment

Model	SIRIO 5	SIRIO 10	SIRIO 15	SIRIO 20
Ean code	8019250199022	8019250199039	8019250199046	8019250199053
Dimensions in cm. (W x H x D)	45 x 42 x 10,2	65 x 42 x 10,2	85 x 42 x 10,2	105 x 42 x 10,2
Power @ 230V	500W	1000W	1500W	2000W
Overall thickness product installed (cm.)	11	11	11	11
Electronic thermostat	•			
Net Weight (Kg)	3,90	5,65	7,15	8,60
Color	White			

Wheels are sold separately. SIRIO height with wheels is 50 cm. Depth is 28,2 cm.

IP24

