


Cellar Grating lock (1 pair) GS 100



for cellar shafts

protects grates from being levered

with escape route lock



ORIGINAL INSTALLATION INSTRUCTIONS



facebook.com/BASIGmbH



[@basi_gmbh](https://instagram.com/basi_gmbh)



www.basi.eu

General notes

Intended use

The grate lock provides additional protection against unauthorised opening of light shaft and cellar shaft covers, and entry to rooms. The ideal level of protection can only be achieved if you follow these assembly and operating instructions appropriately.

The ideal level of protection can only be achieved if you follow these assembly instructions.

Follow the instructions in this manual on how to mount the additional lock correctly. Keep the assembly instructions in a safe place in case you need to remove or replace the additional lock.




Warnings: No hazards are to be expected if the device is used in accordance with the instructions and in a professional manner.

Small parts and packaging materials can be swallowed by children and lead to choking! Make sure that small parts and packaging materials do not get into the hands of children. Dispose of the packaging material immediately.

The GS 100 grate lock protect your grates and cellar shafts from burglars. It can be mounted discreetly at one or several places as required.

- Easy to mount: security can be provided with one or also two systems.
- Easy handling: The locks can be unlocked without a key.

The manufacturer expressly reserves the right to make technical changes.



Disclaimer

The manufacturer accepts no liability for damage and/or injury resulting from improper handling and/or assembly of the product or use of the required tools. If you use power tools (e.g. drill), follow all safety instructions of the tool manufacturer.

Scope of delivery

Check that the delivery is complete:

- 2x stainless steel plate (1)
- 2x bracket (2)
- 2x chain holder (3)
- 2x chain (4)
- 2x mounting plate (5)
- 2x hook (6)
- 2x protection plate (7)
- 2x lock (8)
- 4x screws (9) M5 x 50
- 4x dowel (10)

Required tools

- philips screwdriver or electric screwdriver
- drill with matching bit (6 mm)
- tape measure
- marker pen, scribing needle or similar

General installation tips

- Before installation, make sure that the grate or cellar shaft can be opened and closed easily.
- Use a drilling stop to ensure that the length of the dowels also matches the screws that are used.
- Do not overturn the screws. Use an electric screwdriver with a torque limit, or tighten the screws by hand.
- Please use appropriate attachment material if a plastic cellar shaft is used!
- Please note: The delivery includes two grate locks. If possible, secure the grate on two opposite sides.

Installation steps

1) Place the armour plate (1) onto the grate and insert the bracket (2) into the armour plate.

2) Guide the chain link between the arms of the bracket and affix the chain using the chain holder (3). Pull the chain (4) taut.

3) Thread the hook (6) through the mounting plate (5). Guide the selected chain link across the mounting plate

(5) Pull the chain (4) taut to define the assembly position of the mounting plate (5).

4) Position the mounting plate (5) on top and scratch the positions for the two drill holes. Drill the holes, insert the dowels (10) and attach the mounting plate (5) using the screws (9) so that the chain (4) is taut.

5) Place the chain link over the hook (6), push the protection plate (7) over this and lock it together with the lock (8).

6) Repeat the assembly steps for the second grate lock.

Operation

- To open the grate, unlock the grate locks from inside.

1) Open the lock (8) and remove it with the protection plate (7).

2) Pull the chain link off the hook (6). The chain now hangs freely and the grate can be opened.

To lock the grate again, follow assembly step 5.


Cleaning/maintenance

Slight soiling of the grate lock GS 100 can be removed with a damp cloth.



Disposal

Help to protect the environment and dispose of the product and the packaging materials in accordance with the local regulations.



Technical data

- application area: for securing grates and cellar shaft covers
- chain length approx. 702 mm
- unlocking: without a key
- colour: silver

© Copyright

Reproduction or duplication
(even excerpts thereof)
is forbidden without approval of:
BASI GmbH
Konstantinstraße 387
41238 Mönchengladbach
Germany

2023

This publication, including all its parts,
is protected by copyright.

Any use outside the narrow limits
of copyright law without the consent
of BASI GmbH is not allowed and is
liable to prosecution.

This applies in particular to duplications,
translations, microfilming and importing
and processing in electronic systems.

BASI GmbH
Konstantinstraße 387
41238 Mönchengladbach
Germany