

## Connecting elements H2,5/16T GR BD GSP

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



- Linked wire-end ferrules on reel (5,000 pcs.)
- DIN colour code
- other colour code

### General ordering data

Type	H2,5/16T GR BD GSP
Order No.	<a href="#">1476120000</a>
Version	Wire-end ferrule, insulated, 12 mm, 10 mm, grey
GTIN (EAN)	4050118283020
Qty.	3,000 pc(s).
Packaging	Reel

**Data sheet**

**Connecting elements  
H2,5/16T GR BD GSP**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	16 mm	Width (inches)	0.63 inch
Net weight	0.201 g		

**Technical data**

Version	insulated
---------	-----------

**Wire-end ferrules**

Collar diameter (D2)	4.2 mm	Colour code	Telemecanique
Conductor cross-section	2.5 mm <sup>2</sup>	Contact surface diameter (D1)	2.2 mm
Contact surface length (L2)	10 mm	L1 in mm	16 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.25 mm
Stripping length	12 mm	Wire connection cross section AWG, max.	AWG 14

**Classifications**

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
eClass 5.1	27-40-02-01	eClass 6.2	27-40-02-01
eClass 7.1	27-40-02-01	eClass 8.1	27-40-02-01
eClass 9.0	27-40-02-01	eClass 9.1	27-40-02-01

**Approvals**

Approvals



ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">EPLAN</a>
------------------	-----------------------

**Data sheet**

**Connecting elements  
H2,5/16T GR BD GSP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Similar to illustration**

