

**Industrial Ethernet
IE-FC-DIP-CI/3A/2ST/1D9****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

General ordering data

Type	IE-FC-DIP-CI/3A/2ST/1D9
Order No.	2003370000
Version	FrontCom, Insert plate, unshielded, 1 x GFCL, 1 x fuse, 2x Data, 1x Signal
GTIN (EAN)	4050118387322
Qty.	1 pc(s).

Industrial Ethernet IE-FC-DIP-CI/3A/2ST/1D9

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	90.5 mm	Length (inches)	3.563 inch
Width	116.5 mm	Width (inches)	4.587 inch
Height	23 mm	Height (inches)	0.906 inch
Net weight	141.78 g		

Temperatures

Operating temperature, max.	66 °C	Operating temperature, min.	-35 °C
Operating temperature	-35 °C...66 °C	Storage temperature	
Installation temperature			

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General data

Material	Polycarbonate PC	Product type	Insert plate, unshielded
----------	------------------	--------------	--------------------------

Electrical properties

Operating voltage	125 V AC
-------------------	----------

Standards

Certificate No. (cURus)	E223801
-------------------------	---------

Classifications

ETIM 5.0	EC000456	ETIM 6.0	EC000456
UNSPSC	31-16-23-03	eClass 6.2	27-25-05-04
eClass 7.1	27-18-92-17	eClass 8.1	27-18-92-17
eClass 9.0	27-18-28-06	eClass 9.1	27-18-92-90

Approvals

Approvals



ROHS	Conform
------	---------

Industrial Ethernet IE-FC-DIP-CI/3A/2ST/1D9

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Dimensioned drawing

