

**CRIMPFIX RS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

**General ordering data**

Type	CRIMPFIX RS
Order No.	<a href="#">1477030000</a>
Version	Automatic machines, Automatic stripper and crimper
GTIN (EAN)	4050118284072
Qty.	1 pc(s).

## CRIMPFIX RS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	390 mm	Width (inches)	15.354 inch
Height	430 mm	Height (inches)	16.929 inch
Depth	330 mm	Depth (inches)	12.992 inch
Weight	23 kg	Net weight	23,000 g

### Environmental Product Compliance

REACH SVHC Lead 7439-92-1

### Technical data

Electrical connection 100-240 V / 50/65 Hz

### PW65 maintenance - automatic stripping/crimping

Compressed-air connection	5 bar	Consumables	Linked wire-end ferrules
Crimping length	8/10 mm	Drive	Electropneumatic
Electrical connection	100-240 V / 50/65 Hz	Length of wire-end ferrule	14/16 mm
Pulse time	approx. 1 s	Stripping range	0.5 - 2.5 mm <sup>2</sup>
Wire end ferrules cross-section, max.	2.5 mm <sup>2</sup>	Wire end ferrules cross-section, min.	0.5 mm <sup>2</sup>

### Classifications

ETIM 3.0	EC000163	ETIM 5.0	EC002778
ETIM 6.0	EC002778	UNSPSC	27-11-15-10
eClass 5.1	17-13-01-01	eClass 6.2	17-13-01-01
eClass 7.1	17-13-01-01	eClass 8.1	17-13-01-01
eClass 9.0	17-13-01-01	eClass 9.1	17-13-01-01

### Approvals

Approvals



ROHS Conform

### Downloads

Brochure/Catalogue [CAT 6 TOOLS 15/16 EN](#)  
 User Documentation [Manual](#)

**Data sheet**

**CRIMPFIX RS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Drawings**

