

SAIBW-4/11-T-COD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Type	SAIBW-4/11-T-COD
Order No.	1467890000
Version	Sockets prefabricated to customer spec., Socket, angled
GTIN (EAN)	4050118273625
Qty.	1 pc(s).

SAIBW-4/11-T-COD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	30 g
------------	------

Temperatures

Operating temperature, max.	85 °C	Operating temperature, min.	-40 °C
-----------------------------	-------	-----------------------------	--------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data customisable plug-in connectors

Cable diameter, max.	10 mm	Cable diameter, min.	8 mm
Cable glands	PG 11	Coding	T
Connection cross-section, max.	1.5 mm ²	Connection cross-section, min.	0.5 mm ²
Contact surface	Gold-plated	Housing main material	PA
Insulation strength	10 ⁸ Ω	No. of poles	4
Plugging cycles	≥ 100	Pollution severity	3
Rated current	12 A	Rated voltage	60 V
Shield connection	No	Temperature range of housing	-40 ... +85 °C
Threaded ring material	Diecast zinc	Type of connection	Screw connection

Standards

Certificate No. (cURus)	E307231
-------------------------	---------

Classifications

ETIM 5.0	EC002635	ETIM 6.0	EC002062
eClass 6.2	27-26-07-02	eClass 7.1	27-44-01-02
eClass 8.1	27-44-01-02	eClass 9.0	27-44-01-02
eClass 9.1	27-44-01-03		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 8 SAI 15/16 EN FL FIELDWIRING EN
Engineering Data	STEP
User Documentation	Manual

SAIBW-4/11-T-COD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com**Drawings****Pole scheme**