

**cable lug, terminal end
KWN-M4/-4 90****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KWN-M4/-4 90
Order No.	1495300000
Version	cable lug, terminal end, 4 mm ²
GTIN (EAN)	4050118305081
Qty.	100 pc(s).

**cable lug, terminal end
KWN-M4/-4 90**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data
Dimensions and weights

Weight	0.25 g	Net weight	2.49 g
--------	--------	------------	--------

Technical data

Version	Euro series 90°
---------	-----------------

Connectors

Conductor cross-section	4 mm ²	Connection length (l)	9.5 mm
Flange width (b)	8.5 mm	Hole	M 4
Inside diameter of flange (d2)	4.3 mm	Inside diameter of shaft (d1)	3 mm
Insulation	not available	Outside diameter of shaft (d3)	5 mm
Shaft length (a)	7 mm		

Classifications

ETIM 3.0	EC001509	ETIM 4.0	EC001509
ETIM 5.0	EC001051	ETIM 6.0	EC001051
eClass 6.2	27-40-02-05	eClass 7.1	27-40-02-04
eClass 8.1	27-40-02-05	eClass 9.0	27-40-02-05
eClass 9.1	27-40-02-05		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN

cable lug, terminal end KWN-M4/-4 90

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

