

**ClipCard
CC 85/27 K MC NE GR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



ClipCard device markers in MultiCard format are used for labelling electrical installations and switchgear systems, and offer an interesting alternative to engraving. Thanks to the proven MultiCard format, labelling is possible with PrintJet PRO, the MCP Plus plotter, MCP Basis and MC-Mobilo.

- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- Universal fixing
- Carrier (screwable or with cable ties)
- Tag rail (self-adhesive or screw fixing)
- Or self-adhesive tags

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

Please note that these markers are not intended for printing with the SpeedMarking laser.

General ordering data

Type	CC 85/27 K MC NE GR
Order No.	1526130000
Version	ClipCard, Device markers, 27 x 85 mm, grey
GTIN (EAN)	4050118332162
Qty.	20 pc(s).
compatible printer	1324380000

ClipCard CC 85/27 K MC NE GR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	85 mm	Width (inches)	3.346 inch
Height	27 mm	Height (inches)	1.063 inch
Depth	0.8 mm	Depth (inches)	0.031 inch
Net weight	7.5 g		

General data

Adhesive	Double-sided adhesive tape	Colour	grey
Halogen	No	Material	Polyamide 66
Operating temperature range	-40...60 °C	Recommended industries	Machinery
UL 94 flammability rating	V-2	Version	Self-adhesive
Width	85 mm		

Classifications

ETIM 5.0	EC001288	ETIM 6.0	EC001288
eClass 6.2	27-14-91-29	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-29	eClass 9.0	27-40-06-29
eClass 9.1	27-40-06-29		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP

Data sheet**ClipCard
CC 85/27 K MC NE GR**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings