

ClipCard CC DIA 30/3.5 MC NE RT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The CC DIA 30 MC is used for labelling hydraulic hoses, lights and indicators. Variants with 4.2 mm holes for M4 screws or cable ties can be used for mounting. The variant with 3.5 mm holes is for 3.2 mm blind rivets. According to DIN V VDE V 0108 Part 100 from 01.2010, safety illumination and connection / branch-off point lights which are part of a safety illumination system must be easily and reliably identifiable and marked in red or green. The distributor, electric circuit and lamp ID numbers must be attached next to the lamps.

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	CC DIA 30/3.5 MC NE RT
Order No.	1434110000
Version	ClipCard, Device markers, 30 x 30 mm, With hole, red
GTIN (EAN)	4050118238723
Qty.	60 pc(s).
Alternative product	1266150000
compatible printer	1324380000

ClipCard CC DIA 30/3.5 MC NE RT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	30 mm	Width (inches)	1.181 inch
Height	30 mm	Height (inches)	1.181 inch
Depth	1.2 mm	Depth (inches)	0.047 inch
Net weight	2.15 g	Diameter	30 mm

General data

Application/manufacturer	With hole	Colour	red
Halogen	No	Material	Polyamide 66
Operating temperature range	-40...100 °C	Recommended industries	Machinery
UL 94 flammability rating	V-2	Version	Ø 30 mm, with 3.5 mm mounting hole
Width	30 mm		

Device markers

Diameter	30 mm	Drill-hole diameter	3.5 mm
----------	-------	---------------------	--------

Classifications

ETIM 5.0	EC001288	ETIM 6.0	EC001288
eClass 6.2	27-14-91-29	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-29	eClass 9.0	27-40-06-29
eClass 9.1	27-40-06-29		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP

ClipCard CC DIA 30/3.5 MC NE RT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

