

HSS 0.8-2.4 EL Y30M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The TwinMark endless heat-shrinkable sleeve is labelled within seconds with thermal transfer printing. Depending on the number of characters or the available space, the length of the marker can be individually adjusted and shrunk to fit the conductor. After importing the data with our M-Print® PRO software and printing with the THM Plus S printer, the shrinkable sleeve is perforated to the desired length and is immediately ready to use. An external reel holder (1302920000) has to be used for reels above 30 m printing material.

General ordering data

Type	HSS 0.8-2.4 EL Y30M
Order No.	1505760000
Version	Conductor and cable markers, 0.8 - 2.4 mm, x 4.2 mm, yellow
GTIN (EAN)	4050118314144
Qty.	1 pc(s).
compatible printer	2430920000

HSS 0.8-2.4 EL Y30M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Length	30,000 mm	Length (inches)	1,181.1 inch
Width	4.2 mm	Width (inches)	0.165 inch
Depth	0.77 mm	Depth (inches)	0.03 inch
Net weight	162 g		

General data

Colour	yellow	Halogen	Yes
Length	30,000 mm	Material	Polyolefine
Operating temperature range		Recommended industries	Plant manufacture, Energy, Device manufacturer, Machinery
	-55...135 °C		
Width	4.2 mm		

Conductor and cable markers

Conductor O.D.	0.8 - 2.4 mm	Conductor O.D., max.	2.4 mm
Conductor O.D., min.	0.8 mm	Conductor cross-section, max.	0.5 mm ²
Conductor cross-section, min.	0.25 mm ²	Halogen	Yes
Rate of shrinkage	3:1	Recommended shrinking temperature	90 °C

Classifications

ETIM 5.0	EC001530	ETIM 6.0	EC001530
eClass 6.2	27-40-04-01	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-29	eClass 9.0	27-40-04-01
eClass 9.1	27-40-04-01		

Approvals

Approvals



ROHS

Conform

DownloadsEngineering Data [EPLAN, WSCAD](#)

HSS 0.8-2.4 EL Y30M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Drawings

