

**cable lug, terminal end  
VSRI/1,5-2,5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Insulated cable connector in PVC or PC/PA**

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

**General ordering data**

|            |                                                                                               |
|------------|-----------------------------------------------------------------------------------------------|
| Type       | VSRI/1,5-2,5                                                                                  |
| Order No.  | <a href="#">1491520000</a>                                                                    |
| Version    | cable lug, terminal end, Insulated cable connector, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup> |
| GTIN (EAN) | 4050118301496                                                                                 |
| Qty.       | 50 pc(s).                                                                                     |

## cable lug, terminal end VSRI/1,5-2,5

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

|            |        |
|------------|--------|
| Net weight | 1.36 g |
|------------|--------|

### Connectors

|                               |                     |                                |                     |
|-------------------------------|---------------------|--------------------------------|---------------------|
| Conductor cross-section, max. | 2.5 mm <sup>2</sup> | Conductor cross-section, min.  | 1.5 mm <sup>2</sup> |
| Identification colour         | blue                | Inside diameter of collar (d4) | 5.2 mm              |
| Inside diameter of shaft (d1) | 2.3 mm              | Insulation                     | Fully insulated     |
| Length 1 (l1)                 | 36 mm               | Length 2 (l2)                  | 15 mm <sup>2</sup>  |
| Material/plastic              | Polyethylene        |                                |                     |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 5.0   | EC001059    | ETIM 6.0   | EC001059    |
| eClass 6.2 | 27-40-02-90 | eClass 7.1 | 27-40-02-04 |
| eClass 8.1 | 27-40-02-12 | eClass 9.0 | 27-40-02-12 |
| eClass 9.1 | 27-40-02-12 |            |             |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                    |                                      |
|--------------------|--------------------------------------|
| Brochure/Catalogue | <a href="#">CAT 6 TOOLS 15/16 EN</a> |
|--------------------|--------------------------------------|

### cable lug, terminal end VSRI/1,5-2,5

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

